

00421700 & 00437200 CONNECTORS

7-Pole Plastic Body Sockets • 12V • ISO 1724 • ISO 3732

00421700
00423700

00421900



00421100
00423100

Description

The series consists of a N (Normal) version complying to ISO 1724, which is generally used for standard applications, and a S (Supplementary) version complying to ISO 3732 to be used for additional connections. The latter can easily be recognized by its WHITE colouring and by the different order of the contacts, thus preventing an incorrect connection to the N version. Littelfuse supplies these connectors in plastic body with screw and flat contacts.

Included in the range of sockets are also the following special version with lower body.

Features and Benefits

- Standards: Conforms to ISO 1724 & ISO 3732 recommendations and standards.
- Accepts all 7-pole plugs that conform to ISO 1724 & ISO 3732.
- The screw contacts version is mainly intended for the replacement market (aftermarket)
- The flat terminals version is generally preferred by harness manufacturers.

Ordering Information

| PART NUMBER | | | ISO | PIN MATERIAL | TERMINAL TYPE |
|--------------|---------------|---|------|---------------------|---------------|
| BULK 20 pcs. | BULK 100 pcs. | BULK <input checked="" type="checkbox"/> 100 pcs. | | | |
| 00421700 | 00421790 | 00421799 | 1724 | Brass | screw |
| 00421780 | 00421785 | | 1724 | Nickel plated brass | screw |
| 00421100 | 00421190 | 00421199 | 3732 | Brass | screw |
| | 00421185 | | 3732 | Nickel plated brass | screw |
| 00423700 | 00423790 | 00423799 | 1724 | Brass | flat |
| 00423780 | | | 1724 | Nickel plated brass | flat |
| 00423100 | 00423190 | 00423199 | 3732 | Brass | flat |
| 00421900 | 00421990 | | 1724 | Brass | flat |
| 00425700 | 00425790 | | 1724 | Brass | flat |

Specifications Overview

Voltage: 12V
Standards: ISO 1724
ISO 3732

Web Resources

Download 2D print and technical resources at:
littelfuse.com/connectors

Accessories

| PART NUMBER | IMG. | SOCKET | DESCRIPTION OF ACCESSORIES |
|--------------------|------|--|--|
| 00600400 (20 pcs) | 1 | 00421700 00421780 00421785 00421100 00421185 | Rear rubber gasket for socket with screw terminals |
| 00600460 (200 pcs) | 1 | 00421790 00421190 | Rear rubber gasket for socket with screw terminals |
| 00600500 (20 pcs) | 2 | 00423700 00423780 00423100 00425700 | Rear rubber gasket for socket with flat terminals |
| 00600700 (200 pcs) | 2 | 00423790 00423190 00425790 | Rear rubber gasket for socket with flat terminals |
| 00603200 (1 pcs) | 3 | 00423700 00423100 | Flat terminal coupling for socket |
| 00603260 (100 pcs) | 3 | 00423700 00423100 | Flat terminal coupling for socket |
| 00600600 (1 pcs) | 4 | 00423700 00423100 | Wired flat terminal coupling for socket |

