

DESCRIPTIONPRODUCT COVERED:

USR, CNR - Component - Miniature Fuses, Cat. No. 19354 or 354 rated 1-10 A, 440 V ac and Cat. No. 19356 or 356, rated 1-10 A, 440 V ac, Cat. No. 19358 or 358, rated 3.15-10 A, 500 V ac and 50 V dc.

GENERAL:

These fuses are miniature fuses of the 6.3 by 32 mm size.

USR indicates these products have been evaluated to the requirements of Underwriters laboratories Inc. Standard for Supplemental Fuses, UL 248-14, First Edition.

CNR indicates these products have been evaluated to the requirements of Canadian Standards Association Standard for Supplemental Fuses, CSA-C22.2 No. 248.14-94, First Edition.

MODEL SIMILARITIES:

Cat. Nos. 354 and 356 is identical to Cat. Nos. 19354 and 19356 respectively and was established for marketing purposes only.

INTERRUPTING RATINGS:

These fuses have the following interrupting ratings:

<u>Cat. No.</u>	<u>Ampere Rating</u>	<u>Interrupting Rating</u>
19354, 354	1 - 10 A	1000 A, 440 V ac, resistive
19356, 356	1 - 10 A	1000 A, 440 V ac, resistive
19358, 358	3.15- 10 A	1500 A, 500 V ac, resistive
19358, 358	3.15- 10 A	250 A, 50 V dc, resistive

ENGINEERING CONSIDERATIONS (NOT FOR UL REPRESENTATIVE USE):

These fuses covered by this Report are intended for use as supplementary overcurrent protection where branch circuit or equivalent applications are not involved.

These fuses are for use only in equipment where the suitability of the combination is determined by Underwriters Laboratories Inc.

The above restrictions arise because of the following variations from the Standard for low-voltage fuses, UL 248-1 and UL 248-14, First Editions.

1. These fuses have not been evaluated for the ability to interrupt 10,000 A at 125 V ac, p.f. 0.7-0.8.