



**Underwriters  
Laboratories Inc.®**

**Northbrook Division**  
333 Pfingsten Road  
Northbrook, IL 60062-2096 USA  
www.ul.com  
tel: 1 847 272 8800  
fax: 1 847 272 8129  
Customer service: 1 877 854 3577

LITTELFUSE INC  
MR. BILL TRAVIS, STANDARDS ENGINEER  
800 E NORTHWEST HWY  
DES PLAINES IL 60016

**RE: Project Number(s) - 07NK24412**

Your most recent Certification is shown below. Please review the text and contact the Customer Service Professional who assisted with your project if revisions are required.

To view your company's current Listing Information or for ordering Listing Information in the 3 x 5-inch card format, please refer to [www.ul.com](http://www.ul.com).

**QVGQ2** January 11, 2008  
**Isolated Loop Circuit Protectors - Component**

**LITTELFUSE INC**  
**800 E NORTHWEST HWY, DES PLAINES IL 60016**

**E128662**

Gas tubes, Models SL1001xxx (2-element, mini), SL-1003xxx (3-element, mini), SL-1011xxx (2-element), SL-1018xxx (3-element), SL-1021xxx (3-element), SL-1024xxx (3-element), SL-1026xxx (3-element), SL-1122xxx (3-element, Hybrid); Type 5A(2-element); Model SL1411A followed by 075, 090, 230, 250, 350, 470 or 600, may be followed by A or C; Gas Tubes, 3-electrode axial types, Models SL1403Axx, where suffix xx is 75, 90, 150, 230, 250, 260, 350 or 420.

Models SL0902A followed by 090, 230, 350, 400 or 420, followed by suffix A or SM; Model SL1002A followed by 075, 090, 230, 250, 260, 300, 350, 450, 470 or 600, followed by suffix SM or SP.

Models SL1421A followed by 075, 090, 150, 230, 250, 260, 350, 420, 500 or 600, followed by R, X, P, S or Y.

Gas tube surge arresters, Part No. PMT3(310)-075, -150, -250, -350 or -400; Part Nos. PMT8-090, -150, -230, -250, -350, -400, -500, -600 (voltage breakdown) followed by -01 thru -99 (special customer requirements); Part Nos. PMT10-090, -230, -250, -350, -400, -500, -600. May employ 0, 1, 2 or 3 leads, intended for indoor use only.

Part Nos. CG5-90, CG5-230, CG5-350, CG5-600 may be followed by L, may be followed by TR, may be followed by MS, may be followed by 000 thru 999 for minor variations. Intended for indoor use only.

Part Nos. CG6-90, CG6-230, CG6-350, CG6-500, CG6-600 may be followed by L, may be followed by TR. Intended for indoor use only.

Pill type thyristors, Series P-T070, P-T080, P-T100, 30v-350v; Series P-T100-xxx-003, 6v-315v.

Thyristor type voltage suppressors, axial leads and disc types, Models CRXXX0-SA, -SB, -SC, CRXXX2-AA, -AB, -AC, CRXXX3-AA, -AB, -AC, T10C, T10L Series (100 A), 68v-350v; T10B Series (100 A), 68v-350v; T10A Series (50 A), 68v-270v; T10P Series (100 A), 68v-350v; Surface mount thyristor, SMTBJ Series (50A, 75A or 100A), 50v-200v; bidirectional type, SMT050, SMT100.

Models P6KE6.8A-P6KE440A, 1.5KE6.8A-1.5KE440A, 5KP5.0A-5KP180A, SMBJ5.0A-SMBJ170A, 15KPA17A-15KPA280A, LCE6.5A-LCE28A, SA5.0A-SA180A.

Transient voltage diodes, 5KP Series (5000 W), 5.0v-180v; 288KP170C (288KW); AK6-058C, AK6-076C, AK6-170C, AK6-190C, AK6-240C, AK6-380C, AK6-430C, AK10-058C, AK10-076C, AK10-170C, AK10-190C (NTJ 200), AK10-240C, AK10-380C (NTJ 42), AK10-430C (NTJ 470), P6KE Series (600 W) 6.8v-200v; P6SMBJ Series (600 W), 6.8 V-200V, SA Series (600 W), 5.0v-170v; SMBJ Series (600 W), 5.0v-170v; 1KSMBJ Series (1000 W), 6.8V-100V, 1.5KE Series (1500 W), 6.8v-400v; 15KP Series (15000 W), unidirectional and bidirectional types. Intended for indoor use only.

Marking: Recognized company name or logo, Component Recognition Mark and Part No. designation shall be on the product or smallest shipping package.

**See General Information Preceding These Recognitions**

For use only in equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.

An independent organization working for a safer world with integrity, precision and knowledge

491993001

