

JFHR2.E71611
Special-purpose Fuses - Component

[Page Bottom](#)

Special-purpose Fuses - Component

[See General Information for Special-purpose Fuses - Component](#)

LITTELFUSE INC

E71611

SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

Cartridge fuses, Cat. Nos. KLPC-200 through KLPC-600.

Cat. Nos. L25S001 through L25S800.

Cat. Nos. L50S010 through L50S030.

Cat. Nos. L50S035 through L50S800.

Cat. Nos. L70S001 through L70S800.

Cat. Nos. L17T70 through L17T800A, L17T1200A.

Cat. Nos. LDC150 through LDC600.

Cat. Nos. KLC-0 through KLC-800.

Cat. Nos. TLS1 through TLS125, rated 1-125A, 170 Vdc; TLS-1SA through TLS-125SA, rated 1-125A, Cat. Nos. TLS1 through TLS125, rated 1-125A, 170 Vdc; TLS-1SA through TLS-125SA, rated 1-125A, 170VDC, TLS-1LSE through TLS125LSE rated 1-125A, 170Vdc.

Cat. Nos. TLS-1 through TLS-100L, TLS V1 through TLS V100, TLS1 through TLS100LB, TLS1 through TLS100LS, rated 1-100A, 170 Vdc, TLS-1MB through TLS-100MB, rated 1-100A, 170 Vdc.

Cat. No. TLN 1-600, rated 1-600A, 170V dc.

Type MIDI, Part. Nos. 498 040 through 100 may be followed by M, MXT or MXT-CN.

Series 297 followed by 002 through 030, rated 2-30A, 32 Vdc / 125 Vac.

Series 298 followed by 080 through 200, rated 80-200A, 32 Vdc.

Series 299 followed by 020, 25, 030, 35, 040, 050, 060, 070 or 080, rated 20-80A, 32 Vdc.

Series 999 followed by 020, 025, 030, 035, 040, 050, 060, 070 or 080, rated 20-80A 58 V dc.

Series 446, 447 followed by 002, 003, 004, 005, 07.5 or 010, may be followed by "P", rated 2, 3, 4, 5, 7.5, 10A, 350 Vac; Series 446, 447 followed by 003, may be followed by "P", rated 3A, 140 Vac.

Series 495, J case, followed by 020, 025, 030, 040, 050 or 060, rated 20, 30, 40, 50, 60A, 58 Vdc.

Series 895, low profile J case, followed by 020, 025, 030, 040, 050 or 060, rated 20, 30, 40, 50, 60A, 58 Vdc.

Cat. No. 496, followed by 60, 100, 150 or 200 rated 100, 150 and 200A, 32V dc.

Cat. No. 257APC rated 1-40A, 32 Vdc; Cat. No. 257003 rated 3A, 32 Vdc, 32 Vac.

Cat. No. 287003 rated 3A, 32 Vdc, 32 Vac.

Cat. Nos. JLLS 0-30V, JLLS 0-30LS rated 1-30A, 600 Vac.

Cat. Nos. LVSP-5-2, LVSP-5-R, LVSP-10-2, LVSP-10-R, LVSP-15-2, LVSP-15-R, LVSP-20-2, LVSP-20-R, LVSP-30, LVSP-30-2, LVSP-80, LVSP-80-2, LVSP-100-XL.

Models LVSP-40, LVSP-40-2, LVSP-40-P, LVSP-60, LVSP-60-2.

Fuses for protection of semi-conductor devices, Cat. No. 481 with suffixes 0.18 through 020, rated 125 V ac and 125 dc.

Semi-conductor protection fuses, Cat. Nos. L60S001 through L60S800.

Cat. Nos. L15S001 through L15S1000.

Special purpose cartridge fuses, Cat. No. JLLN, followed -L, -LS, or -V followed by 35 through 60.

Special purpose fuses, Cat. Nos. CNN-10, CNN-35, CNN-40, CNN-50, CNN-60, CNN-80, CNN-90, CNN-100, CNN-125, CNN-150, CNN-175, CNN-200, CNN-225, CNN-250, CN-275, CNN-300, CNN-325, CNN-350, CNN-400, CNN-500, CNN-600, CNN-700, CNN-800, CNL-35, CNL-40, CNL-50, CNL-60, CNL-80, CNL-100, CNL-125, CNL-130, CNL-150, CNL-175, CNL-200, CNL-225, CNL-250, CNL-275, CNL-300, CNL-325, CNL-350, CNL-400, CNL-500.

Cat. Nos. CNN-35 E, CNN-40 E, CNN-50 E, CNN-60 E, CNN-80 E, CNN-90 E, CNN-100 E, CNN-125 E, CNN-150 E, CNN-175 E, CNN-200 E, CNN-225-E, CNN-250 E, CNN-275 E, CNN-300 E, CNN-325 E, CNN-350 E, CNN-400 E, CNN-500 E, CNN-700 E, CNN-800 E.

Cat. Nos. CNL-35E, CNL-40E, CNL-50E, CNL-60E, CNL-80E, CNL-100E, CNL-125E, CNL-130E, CNL-150E, CNL-175E, CNL-200E, CNL-225E, CNL-250E, CNL-275E.

Cat. No. 581, rated 10-800A, 48VDC.

Cat. Nos. KLKD.750.HXL and KLKD005.HXL, rated 3/4A and 5A, 600V AC/DC.

Series 997, rated 2-30 A, 58 Vdc.

Cat. No. SLC-BD rated 50-60A, 480Vac.

Special purpose semi-conductor protection fuses, Cat. Nos. SPFR250, SPFR300, SPFR350, SPFR400.

Series 891 rated 2-30A, 58VDC.

L070SQ30FL0550, rated 550A, 690Vac.

L070SQ32FL1000, rated 1000A, 690Vac.

L125SQ71FL0450, rated 450A, 600Vdc.

L070SQ33FL1100, rated 1100A, 700Vac; L070SQ33FL1250, rated 1250A, 700Vac; L070SQ33FL1400, rated 1400A, 700Vac; L060SQ33FL1500, rated 1500A, 600Vac; L060SQ33FL1800, rated 1800A, 600Vac.

Cat. No. L070SQ30FL0550, rated 550A, 690Vac.

Cat. No. L125SQ71FL0450, rated 450A, 600Vdc.

Cat. No. L070SQ32FL0800, rated 800A, 700Vac; L070SQ32FL1000, rated 1000A, 700Vac; L070SQ32FL1100, rated 1100A, 700Vac.

Cat. No. L50QS, rated 35-800A, 500Vac/500Vdc.

Cat. No. L70QS, rated 35-800A, 700Vac/700Vdc.

Marking: Company name or "LF" and type, series or catalog designation.

Last Updated on 2015-10-30

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2015 UL LLC".