



		REVISION	
REV	DATE	DESCRIPTION	
A	9/7/17	518116GCP - RELEASE MRY	
B	7/9/19	520909ECP/D - UPDATE DIMENSIONS & ADD TOLERANCES MRY	


17.78±0.30
[0.70±0.01]





35.56±0.50
[1.40±0.02]



53.34±0.50
[2.10±0.02]



71.12±0.50
[2.80±0.02]



SPECIFICATIONS:

VOLTAGE RATING: 600V

AMPERE RATING: 30 AMPERES

INTERRUPT RATING: 200kA

WIRE RANGE: #14-8 AWG Cu ONLY

SUGGESTED TORQUE: 2 N-m [17.7 IN-LB]

APPROVALS: UL LISTED (FILE NO. E14721)
CSA CERTIFIED (FILE NO. LR7316)

●	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.		
MATL SPEC		FINISH	
DRW myork	DATE 8/24/17	SCALE NTS	FINISH GOOD WT GRAMS/PIECE
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994			
3RD ANGLE PROJECTION			
TITLE LPSC SERIES OUTLINE			
 CHICAGO, ILLINOIS 60631		REVISION B	DRWG NO. OL-LPSC000

B

SHEET 1 OF 1