



MEDIUM VOLTAGE FUSE CROSS REFERENCE GUIDE

This guide covers the most popular medium voltage fuse types that Littelfuse has in stock and ready to ship within the continental United States! The cross reference is meant to serve as a guide for quick identification and product selection. We suggest you check all applicable specifications before making substitutions.

For fast replacement call our emergency fuse number 24-hours a day [1-800-227-0029](tel:1-800-227-0029)

Competitor	Littelfuse	Notes	Competitor	Littelfuse	Notes	Competitor	Littelfuse	Notes
129D696G05	1706R1C5.5W		677C453G01	5E8PT5.5		C08917P	0700500.Z	Clips for Fuses with ø0.8"
129D696G06	2009R1C5.5W		677C592G04	2E4PT2.4		ECL055-25E	25E1CL5.5	Bussmann: L 16.32" Littelfuse: L 15.13"
15.5CAV0.5	500E11PT15.5	Edison: 80kA I.R. Littelfuse: 35kA I.R.	677C592G09	2E5PT4.8		ECL055-400E	400E2CL5.5	Bussmann: L 21" Littelfuse: L 16.13"
151D241G02	702R1C5.5		678C240G02	20E1C2.75		ECL055-40E	40E1CL5.5	Bussmann: L 16.32" Littelfuse: L 15.13"
151D933G01	2009R1C5.5W		7186A29G02	1E5PT4.8		JCD-2E	2E4PT2.4	
151D933G02	23012R1C5.5W		9F60AAB002	2E4PT2.4		JCE-1E	1E5PT4.8	
151D961G03	39018R2C5.5		9F60BBD001	1E6PT5.5		JCE-2E	2E5PT4.8	
15HLE-125E	125E2C15.5	Littelfuse: 2 barrel design	9F60BHH905	500E11PT15.5		JCJ05.E	500E16PT25.5	
15HLE-30E	30E1C15.5		9F60CCB010	10E1C2.75	Mersen: L 9.18", ø2" Littelfuse: L 10.875", ø3"	JCK-6R	1706R1C2.75	Bussmann: 2.4kV Littelfuse: 2.75kV
15HLE-40E	40E1C15.5		9F60CCB020	20E1C2.75	Mersen: L 9.18", ø2" Littelfuse: L 10.875", ø3"	JCL-18R	39018R2C5.5	
15HLE-80E	80E1C15.5		9F60CED005	5E8PT5.5	Mersen: L 11.18", ø2" Littelfuse: L 9.5", ø1.56"	JCL-2R	702R1C5.5	
177L108G19	1706R1C2.75		9F60CMJ905	500E16PT25.5	Mersen: ø2" Littelfuse: ø1.5625"	JCL-3R	1003R1C5.5	
177L109G16	1003R1C5.5		9F60ECB040	40E1C2.75		JCL-A-12R	23012R1C5.5W	
1A0065	0700300.Z	Clips for Fuses with ø3"	9F60ECB050	50E1C2.75		JCL-A-2R	702R1C5.5W	
1A0065	0700530.Z	Clips for Fuses with ø3"	9F60FJB80	80E1C5.5		JCL-A-4R	1304R1C5.5W	
1A0835	0700156.Z	Clips for Fuses with ø1.5625" to 1.625"	9F60FMH030	30E1C15.5		JCL-A-6R	1706R1C5.5W	
1A1837	0700500.Z	Clips for Fuses with ø0.8"	9F60FMH040	40E1C15.5		JCL-A-9R	2009R1C5.5W	
2123A19G01	2E4PT2.4		9F60HJ100	100E2C25.8		JCQ-5E	5E8PT5.5	
218A4291P02RB	702R1C5.5		9F60LCB806	1706R1C2.75		JCT-½E	500E11PT15.5	
218A4291P18RB	39018R2C5.5		9F61BWW459	0700300.Z	Clips for Fuses with ø3"	JCW-1E	1E6PT5.5	
218A4291P6RA	1706R1C2.75		9F61BWW460	0700156.Z	Clips for Fuses with ø 1.5625" to 1.625"	JCX-10E	10E1C2.75	Bussmann: L 9.19", ø2" Littelfuse: L 10.875", ø3"
228-700-520	0700520.ZXCL	Clip Lock Design Accessory	9F62DCB200	200E1C5.5		JCX-20E	20E1C2.75	
228-700-530	0700530.Z	Clips for Fuses with ø3"	9F62DDD080	80E1C15.5		JCX-40E	40E1C2.75	
2A98253G04	1304R1C5.5W		9F62FCB300	300E2C5.5		JCX-50E	50E1C2.75	
449D361G03	1304R1C5.5W		9F62FCB400	400E2C5.5		JCY-150E	150E1C5.5	
449D362G04	80E1C5.5		9F62FDD125	125E2C15.5		JCY-200E	200E1C5.5	
449D362G07	150E1C5.5		A055C1DORO-25E	25E1CL5.5	Mersen L: 16.12" Littelfuse L: 15.13"	JCY-300E	300E2C5.5	
449D362G08	200E1C5.5		A055C1DORO-400E	400E2CL5.5	Mersen L: 22.12" Littelfuse L: 16.13", 2-barrel	JCY-400E	400E2C5.5	Littelfuse: 2 barrel design Westinghouse: 1 barrel design
449D597G02	702R1C5.5W		A055C1DORO-40E	40E1CL5.5	Mersen L: 16.12" Littelfuse L: 15.13"	JCY-80E	80E1C5.5	
449D597G05	1706R1C5.5W		A055F1DORO-150E	150E1C5.5		JDN-30E	30E1C15.5	
449D797G03	50E1C2.75		A055F1DORO-200E	200E1C5.5		JDN-40E	40E1C15.5	
449D797G11	10E1C2.75		A055F1DORO-80E	80E1C5.5		JDZ-30E	30E1C8.25	
5.5AMWNA1E	1E5PT4.8	Littelfuse: 4.8kV or Less Other: 5.5kV	A055F2DORO-300E	300E2C5.5		MV055F1DAX150E	150E1C5.5	
5.5AMWNA2E	2E5PT4.8	Littelfuse: 4.8kV or Less Other: 5.5kV	A055F2DORO-400E	400E2C5.5		MV055F1DAX200E	200E1C5.5	
5980C20G03	2E5PT4.8		A055F2DORO-400E	400E2C5.5		MV055F1DAX80E	80E1C5.5	
5980C21G03	30E1C8.25		A155F1DORO-30E	30E1C15.5		MV055F2DAX300E	300E2C5.5	
5980C22G04	30E1C15.5		A155F1DORO-40E	40E1C15.5		MV055F2DAX400E	400E2C5.5	
5980C22G08	80E1C15.5		A155F2DORO-125E	15GSE2125E		MV155F1DBX30E	30E1C15.5	
5980C35G01	300E2C5.5		A155F2DORO-80E	80E2C15.5		MV155F1DBX40E	40E1C15.5	
5ACLS-12R	23012R1C5.5W		A240R6R	1706R1C2.75		MV155F1DBX80E	80E1C15.5	
5ACLS-4R	1304R1C5.5W		A240T2E	2E4PT2.4		MV155F2DBX125E	125E2C15.5	
5ACLS-6R	1706R1C5.5W		A480R12R-1HE	23012R1C5.5W				
5ACLS-9R	2009R1C5.5W		A480R18R-1	39018R2C5.5				
5HLE-150E	150E1C5.5		A480R2R-1	702R1C5.5				
5HLE-300E	300E2C5.5		A480R2R-1HE	702R1C5.5W				
5HLE-80E	80E1C5.5		A480R3R-1	1003R1C5.5				
6193403G07	10E1C2.75	GE: ø2" Littelfuse ø3"	A480R4R-1HE	1304R1C5.5W				
6193403G09	20E1C2.75	GE: ø2" Littelfuse: ø3"	A480R6R-1HE	1706R1C5.5W				
6193403G13	50E1C2.75		A480R9R-1HE	2009R1C5.5W				
6293011G08	1E6PT5.5		A480T1E	1E5PT4.8				
677C452G03	500E11PT15.5		A480T2E	2E5PT4.8				
677C452G04	500E16PT25.5		A825X30-1	30E1C8.25				

A fuse may be used in circuits where the fuse voltage rating is equal to or greater than the circuit voltage, unless otherwise stated on the fuse. Never use a fuse in a circuit having a higher rated voltage than the fuse.

For more information or a complete listing of medium voltage fuses offered visit Littelfuse.com/MediumVoltage or call [1-800-TEC-FUSE](tel:1-800-TEC-FUSE).

L = Length
ø = Body Diameter