



Description

250 V BLN Fuses provide low-cost protection for military applications and control circuits.

Electrical Characteristics for Series

% of Ampere Rating	Ampere Rating	Opening Time
100%	0-30	Until temp stabilizes
135%	0-30	1 hours, Maximum
200%	0-30	2 minutes, Maximum


Agency Approvals

Agency	Agency File Number	Ampere Range
	E10480	1.0 - 30A
	LR2 9862	1.0 - 30A
	NBK170305-E10480A-D	5 - 30A


Electrical Specifications by Item

Ordering Number	Amp Rating (A)	Max Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Agency Approvals		
BLN 001	1	250	10,000 amperes at 250 VAC.	.395	x	x	
BLN 01.5	1.5			.222	x	x	
BLN 002	2			.125	x	x	
BLN 003	3			.0645	x	x	
BLN 004	4			.0432	x	x	
BLN 005	5			.0413	x	x	x
BLN 006.	6			.0284	x	x	x
BLN 008	8			.0166	x	x	x
BLN 010	10			.011	x	x	x
BLN 012	12			.00920	x	x	x
BLN 015	15			.00684	x	x	x
BLN 020	20			.0036	x	x	x
BLN 025	25			.00360	x	x	x
BLN 030	30			.00270	x	x	x

Temperature Derating Curve



Average Time Current Curves



Dimensions

