

POLYCAST 200:5 CT TEST

CT: Polycast Industrial Products

ACCUR: 10L20

ID: 932-HBC-05R

SER: 25001-1

RATIO: 200:5

INS.CL: 600 V

This CT was tested with a SE-325. Test results as follows:

SE-325 TRIP SETTING	POLYCAST 200:5 TRIP LEVEL	ACCEPTANCE RANGE
0.5 A	0.49 A	0.4 A to 5.5 A
2.0 A	1.75 A	1.6 A to 2.3 A
4.0 A	3.5 A	3.2 A to 4.4 A

This CT meets the acceptance range specification for the SE-325.