# ISF SERIES
## 250V SHOCK-SAFE AGC (3AG) PANEL-MOUNT GLASS FUSE HOLDER



03453LF2XP

## Specifications

| | |
|---|---|
| **Current Rating Continuous:** | 15A |
| **Current Max:** | 20A |
| **Fuse Type:** | 3AG Glass Fuses |
| **Mounting Method:** | Panel Mount |
| **Housing:** | PA66 GF30 |
| **Recommended Torque:** | Mounting Torque: 15 Lbs.- In. |
| **Max Voltage Rating:** | 250V |

## Description

Compatible with AGC (3AG) glass fuses up to 20 amps, the ISF Series 250V Shock-Safe AGC (3AG) Panel-Mount Glass Fuse Holder features a low-profile body, finger-grip knob, and an anti-tease feature that eliminates circuit interruption when the knob is accidentally depressed.

## Web Resources

Download 2D print, installation guide and technical resources at: **littelfuse.com/ISF**

## Applications

- Hole-Mounted Slow- or Fast-Blowing Automotive Fusing

## Features and Benefits

- Accepts AGC (3AG) glass fuses up to 20 amps (sold separately)
- Shock-Safe fuse holder design eliminates the possibility of electrical shock, as defined in IEC standards 65 and 257
- Anti-tease feature eliminates circuit interruption when the knob is accidentally depressed
- Straight 3/16" Quick Connect terminals for easy wiring
- Low-profile body is easy to install to a panel without a screwdriver
- UL listed and CSA certified

## Ordering Information

| PART NUMBER | DESCRIPTION | FUSE TYPE | MOUNTING METHOD | MAX CURRENT RATING | MAX VOLTAGE RATING |
|---|---|---|---|---|---|
| 03453LF2XP | 250V Shock-Safe AGC (3AG) Panel-Mount Glass Fuse Holder | 3AG GLASS FUSES | PANEL MOUNT | 20 AMPS | 250 V |


© 2021 Littelfuse, Inc.