BOX COVER UNITS



Description

Provide economical method of protecting small motors against overcurrent damage.

Applications


- Edison-Base plug fuses (TOO, TLO)
- Type S plug fuses (SOO, SLO) with adapters (SAO)


Specifications


Voltage Rating 125 V
Max Ampere Rating 15 A
Approvals UL Listed parts (Except LSSY-RL)


Web Resources


Sample requests, downloadable CAD drawings and other technical information: **www.littelfuse.com/boxcover**



Figure 1



Figure 2


Figure 3


Figure 4


Figure 5


Figure 6


Figure 7



Figure 8

FIGURE NUMBER	LITTELFUSE PART NUMBER	BOX COVER FEATURES					TO BE MOUNTED ON
		EDISON BASE FUSE HOLDER	GROUNDING RECEPTACLE	SINGLE POLE SWITCH	TWO POLE SWITCH	PILOT LIGHT	
1	LSOU	1	—	—	—	—	2-1⁄4" Handy Box
	LSOX	1	—	—	—	—	4" Octagon Box
	LSOY	1	—	—	—	—	4" Square Box
2	LSRU*	1	1	—	—	—	2-1⁄4" Handy Box
	LSRW	1	1	—	—	—	2-3⁄4" Switch Box
	LSRY	1	1	—	—	—	4" Square Box
3	LSSU*	1	—	1	—	—	2-1⁄4" Handy Box
	LSSW	1	—	1	—	—	2-3⁄4" Switch Box
	LSSX	1	—	1	—	—	4" Octagon Box
	LSSY*	1	—	1	—	—	4" Square Box
4	LSOY-B	2	—	—	—	—	4" Square Box
5	LSSY-RL	1	1	1	—	1	4" Square Box
6	LSCY	2	—	2	—	—	4" Square Box
7	LSKA	2	1 (250V)	—	—	—	4-11⁄16" Square Box
8	LSTY	2	—	—	1	—	4" Square Box

*UL Listed (File No. E308725)

© 2022 Littelfuse POWR-GARD® Products