
In-Line Cartridge Fuse Holders

155 Series Twist-Lock In-Line Holders for 3AG/AB Fuses

RoHS Pb




Product Characteristics

Compatible Fuses	**For low voltage 3AG/AB or SFE Fuse Applications**
Electrical	Intended for use at 32 volts or less with fuses rated up to 20 amperes when the proper spring is installed for fuse size.
Molded Parts	Black Thermoplastic (UL94 V-2). Body halves have a .14" diameter hole for insulated wire.
Ambient Temperature	–40°C to +75°C.
Contact Rivet	Brass. Nickel plating. Designed to accommodate #14 AWG stranded wire.
Assembled	Supplied with 19" loop of #14 AWG red vinyl insulated wire, SFE fuse (listed) with a spring in different lengths depending of the fuse size.
Unassembled	For assembly to #14 AWG wire.
Options	150 215 is similar to 155 120A except no fuse is supplied. It is intended for use with 3AG fuses rated up to 20 amperes.
In-Line Fuseholder	Supplied with a spring in different lengths depending of the fuse size.

* Please refer to Fuseology section for information on proper fuseholder re-rating.

** Fuseholders with specific wire sizes and lengths are available on special order.

Dimensions



Additional Information

Datasheet | **Resources** | **Samples**

Ordering Information


Unassembled			Assembled			Packaging
Ordering Number	Catalog Number	For Fuse Size	Ordering Number	Catalog Number	Fuse Installed	
-	**155 100**	All below	**01550100Z***	-	-	Bulk Pack (100 Pcs)
01550104ZXU	**155 104U**	¼" × 5/8"	**01550104ZXA**	**155 104A**	SFE 4	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
01550106ZXU	**155 106U**	¼" × ¾"	**01550106ZXA**	**155 106A**	SFE 6	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
01550109ZXU	**155 109U**	¼" × 7/8"	**01550109ZXA**	**155 109A**	SFE 9	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
01550114ZXU	**155 114U**	¼" × 1 1/16"	**01550114ZXA**	**155 114A**	SFE 14	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
01550120ZXU	**155 120U**	¼" × 1 ¼"	**01550120ZXA**	**155 120A**	SFE 20	Bulk Pack (100 Pcs - Assembled) (100 Pcs- Unassembled)
-	-	¼" × 1 1/16"	**01500215Z**	-	-	Bulk Pack (100 Pcs)
		¼" × 1 ¼"				

* Supplied with 8" loop of #14 AWG red vinyl insulated wire and two springs in different lengths to accommodate SFE sized fuses. (Fuse not included)


© 2015 Littelfuse, Inc.
Specifications are subject to change without notice. Application testing is strongly recommended.
Revised: 06/17/15

155 Series Heavy-Duty Bayonet Knob In-Line Holders for 3AG/AB Fuses

RoHS Pb



Dimensions



Product Characteristics

Compatible Fuses	For Low voltage 3AG/AB or SFE Fuse Applications
Electrical	Intended for use at 32 volts or less with fuses rated up to 20 amperes when the proper spring is installed for full size.
Molded Parts	Body and knob are Black Thermoset (UL94 V-0). Both body and knob have a .20" diameter hole for insulated wire.
Knob	Bayonet-lock type metal insert.
Ambient Temperature	–40°C to +125°C.
Contact Rivet	Brass. Tin plated. Designed to accommodate #14 AWG stranded wire.
Assembled	Supplied with 19" loop of #14 AWG red vinyl insulated wire, SFE fuse (listed) with a spring in different lengths depending of the fuse size.
Unassembled	For assembly to #14 AWG wire.
Options	150 079 is similar to 155 020A except no fuse is supplied. It is intended for use with 3AG fuses rated up to 20 amperes.
In-Line Fuseholder	Supplied with a spring in different lengths depending of the fuse size.

* Please refer to Fuseology section for information on proper fuseholder re-rating.

** Fuseholders with specific wire sizes and lengths are available on special order.

Additional Information

Datasheet | Resources | Samples

Ordering Information

Unassembled			Assembled			Packaging
Ordering Number	Catalog Number	For Fuse Size	Ordering Number	Catalog Number	Fuse Installed	
01550004ZXU	**155 004U**	¼" × 5/8"	**01550004ZXA**	**155 004A**	SFE 4	Bulk Pack (100 Pcs)
01550006ZXU	**155 006U**	¼" × ¾"	**01550006ZXA**	**155 006A**	SFE 6	Bulk Pack (100 Pcs)
01550009ZXU	**155 009U**	¼" × 7/8"	**01550009ZXA**	**155 009A**	SFE 9	Bulk Pack (100 Pcs)
01550014ZXU	**155 014U**	¼" × 1 1/16"	**01550014ZXA**	**155 014A**	SFE 14	Bulk Pack (100 Pcs)
01550020ZXU	**155 020U**	¼" × 1 ¼"	**01550020ZXA**	**155 020A**	SFE 20	Bulk Pack (100 Pcs)
-	-	¼" × 1 ¼"	**01500079Z**	-	-	Bulk Pack (100 Pcs)
-	-	¼" × 1 ¼"	**01500145HXB***	-	-	Bulk Pack (100 Pcs)
-	-	¼" × 7/8"	**01500145Z****	-	-	Bulk Pack (100 Pcs)
		¼" × 1 1/16"				
		¼" × 1 ¼"				

* Supplied with 15" loop of #14 AWG red vinyl insulated wire

** and three springs in different lenghts to accommodate SFE sized fuses.

© 2015 Littelfuse, Inc.
Specifications are subject to change without notice. Application testing is strongly recommended.
Revised: 06/12/15

In-Line Cartridge Fuse Holders

Littelfuse
Expertise Applied | Answers Delivered


150 Series In-Line Holders for 2AG or 5×20mm Fuses



Agency Approval

Agency	Agency File Number
c UL us	E14721

Dimensions [mm]



Product Characteristics

Compatible Fuses	**2AG or 5×20mm**
Electrical	This fuseholder, part number 150274, is intended for use with 2AG and 5 × 20mm fuses. Maximum current ratings are 5 amperes at 350V for the 2AG size fuses and 10 amperes at 350V for the 5 × 20mm size fuses.**
Body	Black Nylon, UL94 V-0
Terminals	Brass
Wire	16 Awg size; Nominal o.d. 0.104"; color Red
Lead Pull Test	Will withstand 10 lb. pull.
Ambient Temperature	–40°C to +80°C.

NOTES:
* Ensure that proper fuse re-rating is factored in fuseholder selection.
** If use above 32V, power must be turn off when changing the fuse.

Ordering Information

Ordering Number	Packaging
01500274Z	Bulk Pack (1000 Pcs)
01500274LXN	Bulk Pack (100 Pcs)
***01500274ZXU**	Bulk Pack (5000 Pcs)

NOTES:
* For unassembled Fuseholder, UL certification does not apply.

Additional Information

Datasheet | **Resources** | **Samples**

© 2016 Littelfuse, Inc.
Specifications are subject to change without notice. Application testing is strongly recommended.
Revised: 02/26/16