# SOCKETS

| SOCKETS | | |
|---|---|---|
| Product | Features | Accessory For |
| **OT08PC**<br>Octal Socket 8-Pin  | 8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 600VAC and has pressure clamp terminals. | **AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes. Consult individual datasheet for compatibility** |
| **NDS-8**<br>Octal Socket 8-Pin<br>Screw terminals with captive wire clamps  | 8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC8 hold-down clips. | **Up to two #14 AWG (2.45 mm²) wire size**<br>**Series:**<br>**ARP FS500 LLC4 LLC5**<br>**PRLM TDB TDBH TDBL**<br>**TDI TDIH TDIL TDM**<br>**TDMB TDMH TDML TDR**<br>**TDS TDSH TDSL TRDU**<br>**TRM TRS TRU** |
| **P1011-6**<br>Octal Socket 8-Pin  | 8-pin surface mount socket with binder head screw terminals. Rated at 10A @ 600VAC. UL Listed combination when used with TDM, TDB, TDS Series timers. Uses PSCRB8 hold-down brackets. | **Series:**<br>**ARP FS500 LLC4 LLC5**<br>**PRLM TDB TDM TDMB**<br>**TDR TDS TRB TRDU**<br>**TRM TRS TRU** |
| **OT11PC**<br>Magnal Socket 11-Pin  | Magnal Sockets are for plug-in units | **11-pin Plug-in units**<br>**Series:**<br>**ARP LLC6 TDB TDBH**<br>**TDBL TDMB TDS TDSH**<br>**TDSL TRB TRDU TRM**<br>**TRS TRU** |
| **SD12-PC**<br>Rectangle Socket 12-pin  | 12-pin surface Rectangle Socket. | **ACBC-120** |
| **NDS-11**<br>11-pin Magnal Socket<br>Screw terminals with captive wire clamps  | 11 pin 35 mm DIN rail or surface mount socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC11 hold-down clips. | **AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes**<br>**Series:**<br>**ARP LLC6 TDB TDBH**<br>**TDBL TDMB TDS TDSH**<br>**TDSL TRB TRDU TRM**<br>**TRS TRU** |

© 2016 Littelfuse Protection Relays & Controls