


PART NUMBER	PACKAGING
KR272G0J-1	BULK
KR272G0J-2	TAPE & REEL

RESISTANCE @ +25°C = 2,700 Ω ± 5%
RESISTANCE/TEMPERATURE CURVE = SEE KR272G0J R-T TABLE
BETA "β" (+25 TO +85°C) = 3,750°K NOMINAL
POWER RATING = 240 mW
TEMPERATURE RATING = -40 TO +125°C

PACKAGING: SEE TABLE

ROHS COMPLIANT

SEE MANUFACTURING SPECIFICATION (LAYER 1)

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	04/27/17	DD

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 04/27/17

REV. NONE

LAYER 0 OF 2

U.S. SENSOR CORP.

© COPYRIGHT

714-639-1000 www.ussensor.com

NTC CHIP THERMISTOR

P/N KR272G0J-