

# Certificate



Intertek

for European Product Safety

Reference No. 1010251

## Sub-miniature fuse-link

*Type designation* 392

*Certificate holder* Littelfuse Wickmann  
800 E. Northwest Highway.  
Des Plaines, IL 60016  
UNITED STATES

*The product complies with the standard(s)* EN 60127-3:1996 and A2

*Date of expiry* 31 December 2014

*EU Directive information* The product satisfies the provisions for CE marking according to the Low Voltage Directive 2006/95/EC.

Additional information in Appendix.

*Certification Body* Intertek Semko AB, Product Certification *Place* Kista - Stockholm


*Signed*   
Pär Iggström *Date* 22 February 2010  
Page 1 of 2 

This certificate is issued in accordance with the terms and conditions set out in the Appendix.

**Intertek  
Appendix**

Reference No. 1010251

*Technical data*

Type designation	392
Rated voltage (V)	AC 250 V
Rated current (A)	800 mA; 1 A; 1.25 A; 1.6 A; 2 A; 2.5 A; 3.15 A; 4 A
Standard sheet	4
Brand name:	

*Product information*

Time-lag, low-breaking capacity. Rectangular shape.  
Fuses using lead-free solder.

The sub-miniature fuse-links are tested according to standard sheet 4 with exception of the rated breaking capacity.

The rated breaking capacity is declared by the manufacturer.

Rated breaking capacity:

25 A a.c. and 8 A d.c. (800 mA)

25 A a.c. (1 A; 1.25 A; 1.6 A; 2 A; 2.5 A)

32 A a.c. (3.15 A)

40 A a.c. (4 A)

*Manufacturing site(s)*

LITTELFUSE PHILIPPINES INC  
Lima Technologi Center  
Special Economic Zone  
Lipa City-Malvar, Batangas  
PHILIPPINES

This certificate, which includes production control, is considered to constitute sufficient support for an EC Declaration of Conformity and CE marking of the product according to the Low Voltage Directive 2006/95/EC.

*Certification Body*

Intertek Semko AB, Product Certification

Place Kista - Stockholm

*Signed*
  
Pär Iggström

Date 22 February 2010

*This Certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this certificate. Only the Client is authorized to permit copying or distribution of this certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.*

BSE