SOCKETS

SOCKETS		
Product	Features	Accessory For
OT08PC Octal Socket 8-Pin	8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 600VAC and has pressure clamp terminals.	**AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes. Consult individual datasheet for compatibility**
NDS-8 Octal Socket 8-Pin Screw terminals with captive wire clamps	8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC8 hold-down clips.	**Up to two #14 AWG (2.45 mm²) wire size** **Series:** **ARP FS500 LLC4 LLC5** **PRLM TDB TDBH TDBL** **TDI TDIH TDIL TDM** **TDMB TDMH TDML TDR** **TDS TDSH TDSL TRDU** **TRM TRS TRU**
P1011-6 Octal Socket 8-Pin	8-pin surface mount socket with binder head screw terminals. Rated at 10A @ 600VAC. UL Listed combination when used with TDM, TDB, TDS Series timers. Uses PSCRB8 hold-down brackets.	**Series:** **ARP FS500 LLC4 LLC5** **PRLM TDB TDM TDMB** **TDR TDS TRB TRDU** **TRM TRS TRU**
OT11PC Magnal Socket 11-Pin	Magnal Sockets are for plug-in units	**11-pin Plug-in units** **Series:** **ARP LLC6 TDB TDBH** **TDBL TDMB TDS TDSH** **TDSL TRB TRDU TRM** **TRS TRU**
SD12-PC Rectangle Socket 12-pin	12-pin surface Rectangle Socket.	**ACBC-120**
NDS-11 11-pin Magnal Socket Screw terminals with captive wire clamps	11 pin 35 mm DIN rail or surface mount socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC11 hold-down clips.	**AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes** **Series:** **ARP LLC6 TDB TDBH** **TDBL TDMB TDS TDSH** **TDSL TRB TRDU TRM** **TRS TRU**

© 2016 Littelfuse Protection Relays & Controls