

7-POLE SOCKETS & PLUGS



00590700



00431700



00519700



00516700



00421700



00519200

Description

Menbers 7-Pole sockets and plugs are often used to connect sources and controls for lights in a trailer's electrical system. Available in different wire gauge sizes, as well as in different housing types and interfaces, this portfolio accommodates a number of ISO specifications to fit the need of your vehicle's wiring configuration.

Ordering Information

Ordering Information is displayed on page 2.

Features and Benefits

- Versions available with or without cap to protect against debris intrusion when not in use.
- Screw terminal versions especially suitable for spare & replacement parts markets.
- Mechanical resistance and watertightness guarantee an efficient and reliable electrical connection.

Web Resources

Download installation instructions, 2D prints and technical resources at: littelfuse.com/7-pole-sockets-plugs

7-POLE SOCKETS & PLUGS

Ordering Information

PART NUMBERS	DESCRIPTION	BODY MATERIAL	CABLE OUTLET	CABLE CORES ACCEPTED	ISO	NUMBER OF PINS	TERMINAL MATERIAL	TERMINALS	VOLTAGE
00421700	7P Socket	Plastic	8-9mm	6x1.5mm2, 1x2.5mm2	1724	7	Brass	Screw	12V
00423700	7P Socket	Plastic	8-9mm	6x1.5mm2, 1x2.5mm2	1724	7	Tin-Plated Brass	Flat Terminals 6.3mm	12V
00425700	7P Socket	Plastic	8-9mm	6x1.5mm2, 1x2.5mm2	1724	7	Tin-Plated Brass	Flat Terminals 6.3mm	12V
00401700	7P Socket	Plastic	8-9mm	6x1.5mm2, 1x2.5mm2	1724	7	Brass	Screw	12V
00403700	7P Socket	Plastic	8-9mm	6x1.5mm2, 1x2.5mm2	1724	7	Tin-Plated Brass	Flat Terminals 6.3mm	12V
00516700	7P Plug	Aluminum	8-9mm	6x1.5mm2, 1x2.5mm2	1724	7	Brass	Screw	12V
00585400	7P Socket	Plastic	9mm	6x1.5mm2, 1x2.5mm2	1185	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00586400	7P Socket	Plastic	9mm	4x1.5mm2, 3x2.5mm2	3731	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00585100	7P Socket	Plastic	9mm	6x1.5mm2, 1x2.5mm2	1185	7	Nickel-Plated Brass	Screw	24V
00585200	7P Socket	Plastic	9mm	6x1.5mm2, 1x2.5mm2	1185	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00586100	7P Socket	Plastic	9mm	4x1.5mm2, 3x2.5mm2	3731	7	Nickel-Plated Brass	Screw	24V
00586200	7P Socket	Plastic	9mm	4x1.5mm2, 3x2.5mm2	3731	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00595100	7P Plug	Plastic	9-10.5mm	6x1.5mm2, 1x2.5mm2	1185	7	Nickel-Plated Brass	Screw	24V
00595200	7P Plug	Plastic	9-10.5mm	6x1.5mm2, 1x2.5mm2	1185	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00596100	7P Plug	Plastic	9-10.5mm	4x1.5mm2, 3x2.5mm2	3731	7	Nickel-Plated Brass	Screw	24V
00596200	7P Plug	Plastic	9-10.5mm	4x1.5mm2, 3x2.5mm2	3731	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00431700	7P Socket	Aluminum	8-9mm	6x1.5mm2, 1x2.5mm2	1724	7	Brass	Screw	12V
00433100	7P Socket	Aluminum	8-9mm	2x1.5mm2, 5x2.5mm2	3732	7	Tin-Plated Brass	Flat Terminals 6.3mm	12V
00433700	7P Socket	Aluminum	8-9mm	6x1.5mm2, 1x2.5mm2	1724	7	Tin-Plated Brass	Flat Terminals 6.3mm	12V
00580700	7P Socket	Aluminum	9mm	6x1.5mm2, 1x2.5mm2	1185	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00580900	7P Socket	Aluminum	9mm	6x1.5mm2, 1x2.5mm2	1185	7	Nickel-Plated Brass	Screw	24V
00581000	7P Socket	Aluminum	9mm	6x1.5mm2, 1x2.5mm2	1185	7 16	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00581100	7P Socket	Aluminum	9mm	4x1.5mm2, 3x2.5mm2	3731	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00581600	7P Socket	Aluminum	9mm	4x1.5mm2, 3x2.5mm2	3731	7	Nickel-Plated Brass	Screw	24V
00511700	7P Plug	Plastic	10-12mm	6x1.5mm2, 1x2.5mm2	1724	7	Brass	Screw	12V
00512700	7P Plug	Plastic	10-12mm	6x1.5mm2, 1x2.5mm2	1724	7	Tin-Plated Brass	Flat Terminals 6.3mm	12V
00519000	7P Plug	Plastic	9-10.5mm	6x1.5mm2, 1x2.5mm2	3732	7	Brass	Screw	12V
00519200	7P Plug	Plastic	9-10.5mm	6x1.5mm2, 1x2.5mm2	1724	7	Tin-Plated Brass	Flat Terminals 6.3mm	12V
00519700	7P Plug	Plastic	9-10.5mm	6x1.5mm2, 1x2.5mm2	1724	7	Brass	Screw	12V
00519780	7P Plug	Plastic	9-10.5mm	6x1.5mm2, 1x2.5mm2	1724	7	Brass	Screw	12V
00590700	7P Plug	Aluminum	9-10.5mm	6x1.5mm2, 1x2.5mm2	1185	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00590900	7P Plug	Aluminum	9-10.5mm	6x1.5mm2, 1x2.5mm2	1185	7	Nickel-Plated Brass	Screw	24V
00591100	7P Plug	Aluminum	9-10.5mm	4x1.5mm2, 3x2.5mm2	3731	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00591200	7P Plug	Aluminum	9-10.5mm	6x1.5mm2, 1x2.5mm2	1185	7	Tin-Plated Brass	Flat Terminals 6.3mm	24V
00591600	7P Plug	Aluminum	9-10.5mm	4x1.5mm2, 3x2.5mm2	3731	7	Nickel-Plated Brass	Screw	24V