

Matrix C Ignition

3 Position - (Acc-Off-Run) No Start

Cole Hersee part number	Switch Positions	ACC	OFF	RUN	START	Casing	Stem	Sealing	Anti Restart	Lock Code Type	Key Codes	Key Type	Lever or Hencol Key	Key Blank part number	Affitional Features/Special/Comments
9578	3					Steel	M22x 1.5	Full	Yes	Mixed	CH600-CH799	Boot		83451-6 for 600 series keys 83451-7 for 700 series keys	Replacment boot 81265
95060-06	3	X	X	X		Plastic	M22x 1.5	Full	No	Mixed	CH600-CH799	Boot		83451-6 for 600 series keys 83451-7 for 700 series keys	Replacment boot 81265
75701	3					Steel	M22x 1.5	Full	No	Mixed	CH600-CH799	Boot		83451-6 for 600 series keys 83451-7 for 700 series keys	Replacment boot 81265
75705-01	3					Steel	M22x 1.5	Full	No	Mixed	CH600-CH799	Boot		83451-6 for 600 series keys 83451-7 for 700 series keys	Kit 95060 with conneter and pigail harness Replacment boot 81265

3 Position - (Mom. On-Off-Mom. On) (Glow-Off-Start) & (Off-Run-Start) Momentary Start

Cole Hersee part number	Switch Positions	ACC	OFF	RUN	START	Casing	Stem	Sealing	Anti Restart	Lock Code Type	Key Codes	Key Type	Lever or Hencol Key	Key Blank part number	Affitional Features/Special/Comments
95033	3	Mom	X		Mom	Steel	M22x 1.5	Full	No	Mixed	CH600-CH799	Boot		83451-6 for 600 series keys 83451-7 for 700 series keys	Replacment boot 81265
9513	3		X	X	Mom	diecast	M22x 1.5	Full	No	Mixed	CH600-CH799	Boot		83451-6 for 600 series keys 83451-7 for 700 series keys	Replacment boot 81265
9576	3		X	X	Mom	Steel	1" (25.4mm)	None	No	N/A	N/A	N/A			No lock cylinder, 2 ground terminals connect to housing in start position, blade terminals
95060-03	3		X	X	Mom	Plastic	5/8" (15.9mm)	None	No	Keyed alike	N/A	Hencol	Short		3 terminals
95060-04	3		X	X	Mom	Plastic	5/8" (15.9mm)	O-ring seal in bushing	No	N/A	N/A	Lever	Long		High Current 70A, Anti rotation pin

Cole Hersee part number	Switch Positions	ACC	OFF	RUN	START	Casing	Stem	Sealing	Anti Restart	Lock Code Type	Key Codes	Key Type	Lever or Hencol Key	Key Blank part number	Affitional Features/Special/Comments
95060-60-BP	3		X	X	Mom	Plastic	5/8" (15.9mm)	O-ring seal in bushing	No	Keyed alike	N/A	Hencol	Long		Ground terminal shorts to housing in off position. High current 70A
95514-A	3		X	X	Mom	Steel	5/8" (15.9mm)	O-ring seal in bushing	No	Keyed alike	N/A	Hencol	Short		
95521-01	3		X	X	Mom	Steel	5/8" (15.9mm)	O-ring seal in bushing	No	Keyed alike	N/A	Hencol	Short		
95521-B	3		X	X	Mom	Steel	5/8" (15.9mm)	O-ring seal in bushing	No	Keyed alike	N/A	Hencol	Molded (83355)		Blade terminals
95524-A	3		X	X	Mom	Steel	13/16" (20.6mm)	None	No	10 codes		Metal		83379	
95561-01	3		X	X	Mom	Steel	13/16" (20.6mm)	None	No	Mixed		Metal		83379	No Acc terminal
95534	3					Steel	13/16" (20.6mm)	None	No	10 codes		Metal		83379	
95582	3		X	X	Mom	Steel	3/4" (19.1mm)	None	No	Mixed		Metal		83379	Acc terminal
95591	3		X	X	Mom	Steel	3/4" (19.1mm)	O-ring seal in bushing and gasket seal in base	No	10 codes	CH526-CH536	Metal		83373	
95610	3					Steel	5/8" (15.9mm)	O-ring seal in bushing	No	N/A	N/A	Lever	Long		Silver contacts for higher current
95612	4					Steel	5/8" (15.9mm)	O-ring seal in bushing	No	Keyed alike	N/A	Hencol	Long		Silver contacts for higher current
95613	3		X	X	Mom	Steel	5/8" (15.9mm)	None	No	10 codes		Metal		83379	
956-3122	3		X	X	Mom	diecast	5/8" (15.9mm)	None	No	N/A	N/A	Lever	Short		Silver contacts for higher current. No Acc terminal
956-3124	3		X	X	Mom	diecast	5/8" (15.9mm)	O-ring seal in bushing	No	N/A	N/A	Lever	Short		Silver contacts for higher current. No Acc terminal
956-3125	3		X	X	Mom	diecast	5/8" (15.9mm)	O-ring seal in bushing	No	N/A	N/A	Lever	Short		
956-3126	3		X	X	Mom	diecast	3/4" (19.1mm)	None	No	Mixed	EL101-EL351	Metal		83379	Wires and boot on back
956-3127	3		X	X	Mom	diecast	5/8" (15.9mm)	O-ring seal in bushing	No	Keyed alike	N/A	Hencol	Short		Acc terminal
956-5109	3		X	X	Mom	diecast	15/32" (11.9mm)	None	No	N/A	----	N/A			Magneto toggle ignition switch

Cole Hersee part number	Switch Positions	ACC	OFF	RUN	START	Casing	Stem	Sealing	Anti Restart	Lock Code Type	Key Codes	Key Type	Lever or Hencol Key	Key Blank part number	Affitional Features/Special/Comments
956-5307	3		X	X	Mom	diecast	1" (25.4mm)	O-ring seal in bushing and gasket seal in base	Yes	Mixed		Metal		83373	Ground terminal shorts to housing in Start position,
M-550	3		X	X	Mom	Brass	1" (25.4mm)	O-ring seal in bushing and gasket seal in base	Yes	N/A	N/A	Lever	Short		Ground terminal shorts to housing in Start position,
M-550-14	3		X	X	Mom	Brass	1" (25.4mm)	gasket seal in base	Yes	Mixed		Metal		83373	
M-711	3		X	X	Mom	diecast	1" (25.4mm)	gasket seal in base	Yes	Keyed alike	N/A	Hencol	Short		No Acc terminal
M-850	3		X	X	Mom	Plastic	1" (25.4mm)	O-ring seal in bushing and gasket seal in base	Yes	N/A	N/A	Lever	Short		
95060-05	3		X	X	X	Plastic	3/4" (19.1mm)	None	No	N/A	N/A	Lever	Military		