

GLASS FBG SERIES

32V MULTI-POLE BOLT-DOWN SFE/30410 TYPE GLASS FUSE BLOCK



M-414-01



M-674



M-641-01

Description

The Glass FBG Series 32V Multi-Pole Bolt-Down SFE/30410 Type Glass Fuse Block is compatible with SFE glass fuses and 30410 type circuit breakers (sold separately). This multi-pole automotive glass fuse holder comes in a variety of configurations, including 4-pole, 5-pole, 6-pole, and 8-pole versions. Brass screws and terminals help ensure reliable fuse connections.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/GLASSFBG

Ordering Information

| PART NUMBER | DESCRIPTION | RATING CONTINUOUS | RATING MAX PER CIRCUIT | INPUT TERMINAL | OUTPUT TERMINAL |
|-------------|---|-------------------|------------------------|----------------|-----------------|
| M-414-01 | 30A 4-Pole SFE/30410 Type Glass Fuse Block | 22.5 AMPS | | Screws | Screws |
| M-414-01-BP | 30A 4-Pole SFE/30410 Type Glass Fuse Block - Blister Pack | 22.5 AMPS | | Screws | Screws |
| M-415-01 | 30A 5-Pole SFE/30410 Type Glass Fuse Block | 22.5 AMPS | | Screws | Screws |
| M-641-01 | 30A 6-Pole SFE/30410 Type Glass Fuse Block | 22.5 AMPS | | Screws | Screws |
| M-641-01-BP | 30A 6-Pole SFE/30410 Type Glass Fuse Block - Blister Pack | 22.5 AMPS | | Screws | Screws |
| M-643-01 | 30A 8-Pole SFE/30410 Type Glass Fuse Block | 22.5 AMPS | | Screws | Screws |
| M-643-01-BP | 30A 8-Pole SFE/30410 Type Glass Fuse Block - Blister Pack | 22.5 AMPS | | Screws | Screws |
| M-674 | 50A 4-Pole SFE/30410 Type Glass Fuse Block | 37.5 AMPS | 20 AMPS | Screws | Screws |
| M-674-BP | 50A 4-Pole SFE/30410 Type Glass Fuse Block - Blister Pack | 37.5 AMPS | 20 AMPS | Screws | Screws |

Specifications

| | |
|--------------------------|----------------------------|
| Max Voltage: | 32VDC |
| Current Rating: | 30A, 50A |
| Fuse Type: | Glass SFE or 30410 |
| Mounting Method : | Cartridge Glass Tube Clips |

Applications

- Accessory Circuits
- Classic Cars
- Marine

Features and Benefits

- Accepts SFE glass fuses and 30410 type circuit breakers (sold separately)
- Bolt-down mountable, multi-pole fuse block holds multiple automotive glass fuses
- Available in a variety of configurations, including 4-pole, 5-pole, 6-pole, and 8-pole fuse block options
- 4-pole glass fuse blocks are available with a 30A max current rating or a 50A max current rating
- Brass screws and terminals