

# 15500 Series

## Heavy-Duty Bayonet Knob In-Line Holders for 3AG/AB Fuses



### Product Characteristics

Compatible Fuses	For Low voltage 3AG/AB or SFE Fuse Applications
<b>Electrical</b>	Intended for use at 32 volts or less with fuses rated up to 20 amperes when the proper spring is installed for full size.
<b>Molded Parts</b>	Body and knob are Black Thermoset (UL94 V-0). Both body and knob have a .20" diameter hole for insulated wire.
<b>Knob</b>	Bayonet-lock type metal insert.
<b>Ambient Temperature</b>	-40°C to +125°C.
<b>Contact Rivet</b>	Brass. Tin plated. Designed to accommodate #14 AWG stranded wire.
<b>Assembled</b>	Supplied with 19" loop of #14 AWG red vinyl insulated wire, SFE fuse (listed) with a spring in different lengths depending of the fuse size.
<b>Unassembled</b>	For assembly to #14 AWG wire.
<b>Options</b>	150 079 is similar to 155 020A except no fuse is supplied. It is intended for use with 3AG fuses rated up to 20 amperes.
<b>In-Line Fuseholder</b>	Supplied with a spring in different lengths depending of the fuse size.

\*Refer to [Fuseology](#) for information on proper fuseholder re-rating.

### Additional Information



Resources




Accessories



Samples

### Dimensions



### Ordering Information

Unassembled			Assembled			Packaging
Ordering Number	Catalog Number	For Fuse Size	Ordering Number	Catalog Number	Fuse Installed	
01550004ZXU	155 004U	¼" × 5/8"	01550004ZXA	155 004A	SFE 4	Bulk Pack (100 Pcs)
01550006ZXU	155 006U	¼" × ¾"	01550006ZXA	155 006A	SFE 6	Bulk Pack (100 Pcs)
01550009ZXU	155 009U	¼" × 7/8"	01550009ZXA	155 009A	SFE 9	Bulk Pack (100 Pcs)
01550014ZXU	155 014U	¼" × 1 1/16"	01550014ZXA	155 014A	SFE 14	Bulk Pack (100 Pcs)
01550020ZXU	155 020U	¼" × 1 ¼"	01550020ZXA	155 020A	SFE 20	Bulk Pack (100 Pcs)
-	-	¼" × 1 ¼"	01500079Z	-	-	Bulk Pack (100 Pcs)
-	-	¼" × 1 ¼"	01500145HXB*	-	-	Bulk Pack (100 Pcs)
-	-	¼" × 7/8"	01500145Z**	-	-	Bulk Pack (100 Pcs)
-	-	¼" × 1 1/16"				
-	-	¼" × 1 ¼"				

\* Supplied with 15" loop of #14 AWG red vinyl insulated wire

\*\* Supplied with 15" loop of #14 AWG red vinyl insulated wire and three springs in different lengths to accommodate SFE sized fuses.

**Warning:** Electrical Shock. Power must be disconnected prior to handling fuse.

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).