

# MAXI® MAB SERIES

## IN-LINE SCREW TERMINAL FUSE HOLDER



01520001TXN

### Description

The MAXI® MAB Series 32V In-Line Screw Terminal Fuse Holder is designed to safely and easily replace hard-to-change fusible link wire. Compatible with up to 60-amp MAXI® blade fuses (sold separately), this automotive fuse holder is ideal for high-amp audio circuit protection.

An available dust cover helps safeguard the installed fuse from debris, while the interlocking fuse holder block feature allows 2-pole installation.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/MAB](https://www.littelfuse.com/MAB)

### Ordering Information

| PART NUMBER    | DESCRIPTION   | CURRENT RATING MAX | FUSE TYPE | MOUNTING METHOD     | MAX VOLTAGE RATING |
|----------------|---|--------------------|-----------|---------------------|--------------------|
| 01520001TXN    | 32V In-Line Screw Terminal Fuse Holder - 100 Pcs.                                   | 60 Amps            | MAXI      | In-Line Fuse Holder | 32V                |
| 01520001TXN940 | 32V In-Line Screw Terminal Fuse Holder with Screws and Terminals - 200 Pcs.         | 60 Amps            | MAXI      | In-Line Fuse Holder | 32V                |
| 01520001TXN941 | 32V In-Line Screw Terminal Fuse Holder with Screws, Terminals, and Cover - 100 Pcs. | 60 Amps            | MAXI      | In-Line Fuse Holder | 32V                |
| 01520001U      | 32V In-Line Screw Terminal Fuse Holder - 500 Pcs.                                   | 60 Amps            | MAXI      | In-Line Fuse Holder | 32V                |
| 01520900H      | Protective Fuse Holder Cover - 500 Pcs.   | -                  | -         | -                   | -                  |
| 01520900TXN    | Protective Fuse Holder Cover - 500 Pcs.   | -                  | -         | -                   | -                  |
| 01520900U      | Protective Fuse Holder Cover - 500 Pcs.   | -                  | -         | -                   | -                  |
| 0MAB0001F      | 32V In-Line Screw Terminal Fuse Holder with Screws - 200 Pcs.                       | 60 Amps            | MAXI      | In-Line Fuse Holder | 32V                |
| 0MAB0001XP     | 32V In-Line Screw Terminal Fuse Holder with Screws - Blister Pack - 5 Pcs.          | 60 Amps            | MAXI      | In-Line Fuse Holder | 32V                |

### Specifications

|                             |   |
|-----------------------------|---|
| <b>Current Rating Max:</b>  | 60 Amps   |
| <b>Fuse Type:</b>           | MAXI  |
| <b>Flammability Rating:</b> | UL 94 V-2   |
| <b>Input Terminals:</b>     | <b>Recommended:</b><br>2.5 -6 MM <sup>2</sup> (DIN 46234)<br>6 -10 MM <sup>2</sup> (DIN 46234)                        |
| <b>Mounting Method:</b>     | In-Line Fuse Holder<br><b>Recommended:</b><br>2.5 -6 MM <sup>2</sup> (DIN 46234)<br>6 -10 MM <sup>2</sup> (DIN 46234) |
| <b>Max Voltage Rating:</b>  | 32V   |
| <b>Wire Description:</b>    | <b>Recommended:</b> Cable Cross Section   |
| <b>Wire Size:</b>           | <b>Recommended in MM<sup>2</sup>:</b><br>2.5, 4, 6 and 10   |

### Applications

- High-Amp Audio Circuit Protection

### Features and Benefits

- Compatible with MAXI® blade fuses up to 60 amps (sold separately)
- Interlocking fuse holder block feature enables 2-pole installation
- Screw terminals make in-line installation easy
- Available dust cover helps protect the installed fuse
- UL 94 V-2 flammability rating