

# 08095500 & ... BATTERY DISCONNECT SWITCHES

## Accessories for electrical battery disconnect switches



08095500



00225800



00603800



00902900



00226200



00226600



00227400



00900400



00900500



00900600



00900700



00900900



00901600



00902800



00903100

## Ordering Information

PART NUMBER	PACKAGING CONTENT	DESCRIPTION	MATERIAL	BATTERY SWITCHES APPLICATION
08095500	2 pcs.	Rubber protection cap	Grommet	M10-M12 contact
00225800	2 pcs.	Stiff protection sheath for NW17 corrugated pipe	Plastic	08094461-08094562-08094563
00603800	10 pcs.	Rubber protection cap	Grommet	08094461-08094562-08094563
00902900	1 pcs.	Protection cover	Plastic	08094561-08094860-08094960
00226200	2 pcs.	Stiff protection sheath for NW22 corrugated pipe	Plastic	08097362-08097461-08097462
00226600	2 pcs.	Stiff protection sheath closed	Plastic	08091761
00227400	1 pcs.	8-pole plug (8x1,6 mm)	Plastic	08097860-08095800-08095890-08095900-08095990-08096400-08096490-08096500-08096590
00900400	1 pcs.	Black button for activation	Metal	08070000-08070100-08070060-08070160-08094270-08095800-08095890-08095900-08095990-08096400-08096490-08096500-08096590-08096561-08096562-08096563
00900500	1 pcs.	Protection cover for emergency switch on-cab with screws	Plastic	Electrical battery switches
00900600	1 pcs.	Metallic bracket	Metal	08098100
00900700	1 pcs.	Metallic bracket	Metal	08098100
00900900	1 pcs.	Emergency switch-on red button	Metal	Electrical battery switches
00901600	1 pcs.	Double pole changeover button	Metal	Magnetic battery switches retention
00902800	1 pcs.	Protection cover	Plastic	08098160-08097368-08097468

## 08095500 & ... BATTERY DISCONNECT SWITCHES

### Accessories for electrical battery disconnect switches



### Ordering Information

PART NUMBER	PACKAGING CONTENT	DESCRIPTION	MATERIAL	BATTERY SWITCHES APPLICATION
08095400	1 pcs.	Electrical wiring with 8 pole	-	08097860-08095800-08095890-08095900-08095990-08096400-08096490-08096500-08096591-08096562-08096590
00226800	1 pcs.	4-pole plug according DIN 72585	Plastic	08097161-08097262-08091761-08097460-08097464-08097364
00227300	1 pcs.	7-pole plug	Plastic	0809736-08097367-08097463-08097467-08097469
00227700	1 pcs.	4-pole male connector	Plastic	08070000-08070100-08070060-08070160
00227100	1 pcs.	Stiff protection sheath	Plastic	08096561
00227900	1 pcs.	8-pole plug (7x1,6 mm +1x3,5 mm)	Plastic	08096563
00900800	1 pcs.	Green control light (LED)	-	08095800-08095890-08095900-08095990-08096400-08096490-08096500-08096591-08096562-08096590
00901000	1 pcs.	Green button for battery switch activation	Metal	ADR version
08096300	1 pcs.	P.V.M. 4 module	-	ADR version
07590700	1 pcs.	Earth contact strip length 880 mm section mm <sup>2</sup> 20	Copper moulded	ADR version
00226700	2 pcs.	Stiff protection sheath	Plastic	08097469
00901400	1 pcs.	Metallic bracket	Metal	08097364-08097464
00901500	1 pcs.	Change over contact (ON)-OFF-(ON)	Plastic	08097367-08097463-08097467-08097469-08097363
00121400	1 pcs.	1A fuse holder for ADR application	Plastic	ADR version
00712500	1 pcs.	4 pole plug female wiring	-	08075161-08075163 (WatchDog)
00712600	1 pcs.	7 pole plug female wiring	-	08075161-08075163 (WatchDog)