

LF SERIES FUSE BLOCK COVERS



Description

Littelfuse fuse block covers protect personnel from accidentally coming into contact with energized parts. Covers are for use with Littelfuse UL class fuse blocks. Review the ordering information or contact the factory for available covers

Specifications

Connection

Snap to fuse body

Molded Base

Black thermoplastic

Flammability Rating

UL94 V-0

Approvals

UL Listed (File: E184929)

CSA Certified

(File: 007316_0_000 Class 6225-01)

Features/Benefits

- Added safety to personnel
- Ventilated to avoid fuse derating
- Reusable
- UL listed and CSA certified
- Available for Class H/R, Class J, Class T and Class CD
- Convenient snap-on feature
- Allows visibility of indicator fuse block light

Web Resources

Downloadable CAD drawings, dimensions and other technical information, visit

Littelfuse.com/fuseblocks

Ordering Information

UL CLASS	FUSE BLOCK BASE PART NUMBER*	VOLTAGE	AMPERAGE	COVER ORDERING NUMBER
Class H/R	LFH25030 / LFR25030	250	30	LFH25030FBC
Class H/R	LFH25060 / LFR25030	250	60	LFH25060FBC
Class H/R	LFH25100 / LFR25100	250	100	LFH25100FBC
Class H/R	LFH60030 / LFR60030	600	30	LFH60030FBC
Class H/R	LFH60060 / LFR60060	600	60	LFH60060FBC
Class H/R	LFH60100 / LFR60100	600	100	LFH60100FBC
Class J	LFJ60030	600	30	LFJ60030FBC
Class J	LFJ60060	600	60	LFJ60060FBC
Class J	LFJ60100	600	100	LFJ60100FBC†
Class T	LFT30030	300	30	LFT30030FBC
Class T	LFT30060	300	60	LFT30060FBC
Class T	LFT30100	300	100	LFT30100FBC
Class T	LFT60030	600	30	LFT60030FBC
Class T	LFT60060	600	60	LFT60060FBC
Class T	LFT60100	600	100	LT60100FBC
Class T	LFT60200	600	200	LT60200FBC
Class T	LFT60400	600	400	LT60400FBC
Class T	LFT60600	600	600	LT60600FBC
Class CD	LFC60060	600	60	LFC60060FBC
Class CC	L60030C	600	30	SPL001







* Part number shown excludes reference to number of poles and terminal type

† Cover is not compatible with 70-100 A JLS series fuses

LF SERIES FUSE BLOCK COVERS

Dimensions in mm (inches)

Class H/R


250 V 30 A**250 V 60 A****250 V 100 A****600 V 30 A****600 V 60 A****600 V 100 A**Also available at Littelfuse.com/fuseblocks

LF SERIES FUSE BLOCK COVERS


Dimensions in mm (inches)

Class J


600 V 30 A



600 V 60 A




600 V 100 A




Dimensions in mm (inches)

Class T


300 V 30 A



300 V 60 A



300 V 100 A




LF SERIES FUSE BLOCK COVERS


Dimensions in mm (inches)

Class T


600 V 30 A




600 V 60 A




600 V 100 A




600 V 200 A



600 V 400 A



600 V 600 A



Dimensions in mm (inches)

Class CD

600 V 60 A

