

# LRU SERIES FUSE REDUCERS



## Description

Littelfuse® fuse reducers allow smaller ampere fuses to be installed into existing fuse clips to prevent overfusing.

## Features/Benefits

- Simple installation
- Reduces inventory requirements
- Silver brazed joints for maximum strength
- UL Listed (File No. E136855)
- CSA Certified (File No. 604107)

## Web Resources

Downloadable CAD drawings, FAQs, and other technical information visit: [Littelfuse.com/lruh](http://Littelfuse.com/lruh)

[Littelfuse.com/lrir](http://Littelfuse.com/lrir)

[Littelfuse.com/lruj](http://Littelfuse.com/lruj)

Refer to fuse section of this catalog for fuse dimensions.

## Ordering Information

### 250 Volt

| CATALOG/ORDERING NUMBER |             | FUSE CLIP | FUSE CASE SIZE |
|-------------------------|-------------|-----------|----------------|
| CLASS H/K5              | CLASS R     |           |                |
| LRU 263                 | LRU 263 R   | 60 A      | 30 A           |
| LRU 213                 | LRU 213 R   | 100 A     | 30 A           |
| LRU 216                 | LRU 216 R   | 100 A     | 60 A           |
| LRU 226                 | LRU 226 R   | 200 A     | 60 A           |
| LRU 2621                | LRU 2621 R  | 200 A     | 100 A          |
| LRU 2641                | LRU 2641 R  | 400 A     | 100 A          |
| LRU 2642                | LRU 2642 R  | 400 A     | 200 A          |
| LRU 2661                | LRU 2661 R  | 600 A     | 100 A          |
| LRU 2662                | LRU 2662 R  | 600 A     | 200 A          |
| LRU 2664                | LRU 2664 R* | 600 A     | 400 A          |

\*Only one reducer required.

### 600 Volt

| CATALOG /ORDERING NUMBER |             |         | FUSE CLIP | FUSE CASE SIZE |
|--------------------------|-------------|---------|-----------|----------------|
| CLASS H/K5               | CLASS R     | CLASS J |           |                |
| LRU 663                  | LRU 663 R   | LRUJ63  | 60 A      | 30 A           |
| LRU 216                  | LRU 216 R   | LRUJ13  | 100 A     | 30 A           |
| LRU 616                  | LRU 616 R   | LRUJ16† | 100 A     | 60 A           |
| LRU 626                  | LRU 626 R   | LRUJ26  | 200 A     | 60 A           |
| LRU 2621                 | LRU 2621 R  | LRUJ21  | 200 A     | 100 A          |
| LRU 2641                 | LRU 2641 R  | LRUJ41  | 400 A     | 100 A          |
| LRU 2642                 | LRU 2642 R  | LRUJ42  | 400 A     | 200 A          |
| LRU 2661                 | LRU 2661 R  | —       | 600 A     | 100 A          |
| LRU 2662                 | LRU 2662 R  | —       | 600 A     | 200 A          |
| LRU 2664                 | LRU 2664 R† | LRUJ64  | 600 A     | 400 A          |

†Only one reducer required.

†Fuse and reducer combination is slightly larger in diameter than 100 A Class J fuses. For specific applications, contact factory.

Class J reducers cannot be used in bolt-on applications.

## Recommended Fuses

### Class H/K5 Fuse Reducers

250V - NLN

600V - NLS

### Class R Fuse Reducers

250V - FLNR / FLNR\_ID / LLNRK / KLNR

600V - FLSR / FLSR\_ID / IDSR / LLSRK / LLSRK\_ID / KLSR

### Class J Fuse Reducers

JTD\_ID / JTD

JLS