Littelfuse® | Cole Hersee® A Littelfuse® Brand

www.Littelfuse.com/aftermarket

New Littelfuse & Cole Hersee Retail Packaged Product Offerings

Additional popular Littelfuse and Cole Hersee products are now in retail blister packaging enabling showroom and retail display.

SR Series
Master Battery Disconnect Switch



Part No: 880062-BP

- 300A at 32V DC
- 3500A Max Current Rating
- 300A Continuous Current & 3500A for 2 Second Intermittent Current
- SPST, ON-OFF
- IP67 / IP69K Ingress Protection
- Stainless Steel Hardware and 3/8"-16 Tin-Plated Copper Studs

Littelfuse.com/SR

Continuous Duty
Solenoid Relay



Part No: 24213-BP

- 200A at 12V DC
- SPST, Continuous Duty
- Terminals: Two Steel 5/16"-24 studs, Two Steel #10-32 studs
- Silver plated contacts

Littelfuse.com/ContinuousDuty

2484 Series
Battery Disconnect Switch



Part No: 2484-BP

- Continuous Current: 40A at 6V DC, 20A at 12V DC
- Intermittent Current: 250A at 6V DC, 125A at 12V DC
- 6-12V DC, Two Position, SPST
- Terminals: Two copper 3/8"-24 studs

Littelfuse.com/2484

Solenoid
Continuous Duty Reversing Relay



Part No: 24450-BP

- 75A at 12V 5 min ON/5 min OFF, 125A at 12V 30 sec, 150A at 12V 0.5 sec
- Intermittent Duty, DPDT, Normally Open
- With dynamic braking capability
- Four 5/16"-24 Copper Studs

Littelfuse.com/RevSolenoid

956 Heavy Duty Series
Rotary Ignition Switch



Part No: 956-3126-BP

- 3 Position: Off-Ign/Acc-Ign/Start
- Rated up to 10A at 12V
- 4 Brass Screw Terminals
- Start Lockout: Switch must go to OFF position before the start circuit can be re-energized
- Fits panels up to 0.76" (2.28mm) thick
- Complies with SAE J259

Littelfuse.com/956Series

Standard Heavy Duty
Weather Resistant Toggle Switch



Part No: 5582-10-BP

- SPST: Single Pole, Single Throw, On-Off
- Rated up to 25A at 12V DC
- Mounting: 15/32"-32 thread, 15/32" (11.90mm) long
- Fits panels up to 1/4" (6.35mm) thick
- 2 Wire Leads, 8" long (203.2mm), 16AWG
- Nickel-plated brass handle 0.69" (17.52mm)

Littelfuse.com/StandardDuty

Find additional photos, specifications, and datasheets by visiting www.littelfuse.com/aftermarket

Littelfuse® | Cole Hersee® A Littelfuse® Brand

www.Littelfuse.com/aftermarket

MEGA Flex Series
MEGA® Bolt-Down Fuse Block



Part No: 02981028-BP

- Rated for MEGA fuses 500A at 32V DC
- Flexible cover allows for universal installation
- Dovetail locks allow holders to stack
- M8 Terminal Studs
- M6 Mounting Holes

Littelfuse.com/Mega-Flex

MIDI Flex Series
MIDI® Bolt-Down Fuse Block



Part No: 04981038-BP

- Rated for MIDI fuses up to 200A at 32V DC
- Flexible cover allows for universal installation
- Dovetail locks allow holders to be stacked
- M5 Terminal Studs
- M4 Mounting Holes

Littelfuse.com/Midi-Flex

MAH Series
MAXI Style In-Line Fuse Holder



Part No: MAHC-BP

- Rated for MAXI fuses 20 to 60A at 32V DC
- 5" UL3288 Wire Leads
- Designed for medium current loads
- In-Line holders allow for universal mounting

Littelfuse.com/MAH

MIDI-498 Series
MIDI Bolt Down Fuse Block



Part No: 04980903-BP

- Rated for MIDI fuses 30 to 200A at 32V DC
- Dovetail locks allow holders to be stacked
- M5 Terminal Studs
- M4 Mounting Holes

Littelfuse.com/Midi-498

Sealed ATO In-Line Series
Sealed HD ATO In-Line Fuse Holder



Part No: FHAS100-BP

- Rated for ATO fuses up to 30A at 32V DC
- Rated IP67 with sealed cover for moisture & dust resistance
- Includes two tinned 8" Red GXL wire leads for easy in-line installation

Littelfuse.com/SealedATO-MINI

Sealed MINI In-Line Series
Sealed HD MINI In-Line Fuse Holder



Part No: FHMS200-BP

- Rated for MINI fuses up to 30A at 32V DC
- Rated IP67 with sealed cover for moisture & dust resistance
- Includes two tinned 8" Red GXL wire leads for easy in-line installation

Littelfuse.com/SealedATO-MINI

Commercial and Fleet Vehicle
Emergency Fuse Kit



Part No: 00941003Z

- This convenient kit contains thepopular amperage fuses for most vehicle types along with two fuse pullers

Trailer Connector Holder
Universal 7P and 13P



Part No: 11750-BP

- Stores plugs while not in use and extends electrical connection life by keeping contacts free from dirt and water
- Impact-resistant, heavy duty glass-filled housing is spring loaded for secure locking

Littelfuse.com/11750