

UL Product iQ™



IZLT2.E14721 - Fuseholders, Cartridge Fuse - Component

Fuseholders, Cartridge Fuse - Component

See General Information for Fuseholders, Cartridge Fuse - Component

LITTELFUSE INC

SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

E14721

Cat. No.	Voltage Rating (V)	Current Rating (A)	Withstand Rating RMS Symmetrical	Fuse Class or Size
OPTF0015P	250ac/dc	18	-	-
OPTF0030M	250ac/dc	20	-	-
OPTF0035M	250ac/dc	20	-	-
OPTF0045M	250ac/dc	20	-	-
OPTF0050M	250ac/dc	20	-	-
OPTF0060W	250ac/dc	20	-	-
OPTF0070M	250ac/dc	20	-	-
OPTF0075P	250ac/dc	20	-	-
OPTF0078P	250ac/dc	20	-	-
OPTF015BP	250ac/dc	18	-	-
OPTF015SP	250ac/dc	18	-	-
100020 with or without suffix letters and/or one prefix letter	600ac	20	-	5mm dia.
100058	1000ac	15	-	-
102071	1000ac	15	-	-
102074	1000ac	15	-	-

102076	1000ac	15	-	-
102078	1000ac	15	-	-
102079	1000ac	15	-	-
102080	1000ac	15	-	-
105003 With or without one prefix and with or without additional suffixes	0ac	30	-	-
105013 With or without one prefix and with or without additional suffixes	0ac	30	-	-
111501	1000ac	10	-	-
122055	1000ac	30	-	-
122083	1000ac	30	-	-
122087	1000ac	30	-	-
122088	1000ac	30	-	-
122090	1000ac	30	-	-
122093	1000ac	30	-	-
122094	1000ac	15	-	-
1240040 with or without suffix letters and/or one prefix letter	0ac/dc	63	-	10 mm
1240041 with or without suffix letters and/or one prefix letter	0ac/dc	63	-	10mm
1240060 with or without suffix letters and/or one prefix letter	0ac/dc	40	-	6.3mm
1240061 with or without suffix letters and/or one prefix letter	0ac/dc	40	-	6.3mm
125003 With or without one prefix and with or without additional suffixes	0ac	60	-	-
125004 with or without additional suffixes	1500ac/dc	30	-	10mm
125005 with or without additional suffixes	1500ac/dc	30	-	10mm

125013 With or without one prefix and with or without additional suffixes	0ac	60	-	-
1500312 with or without suffix letters and/or one prefix letter	500ac	15	10000	1/4 in. x 1-1/4 in
150274 with or without suffix letters and/or one prefix letter	350dc	10	10000	5 mm x 20 mm
	350ac	10	10000	4.5mm x 15 mm
150322 with or without suffix letters and/or one prefix letter	500ac	15	10000	1/4 in. x 1-1/4 in
150332 with or without suffix letters and/or one prefix letter	500ac	15	10000	1/4 in. x 1-1/4 in
150603 maybe followed by additional suffix letters and/or one prefix letter.				
	600ac/dc	20	10000	3AB/3AG
150605	600ac/dc	20	10000	5mm x 20mm
1530031#	32ac	20	-	Mini Fuse, 10.92 by 16.25 by 3.81 mm
1530032#	32ac	20	-	Mini Fuse, 10.92 by 16.25 by 3.81 mm
1530033#	32ac	20	-	Mini Fuse, 10.92 by 16.25 by 3.81 mm
153007	32ac	20	10000	Supplemental
153008	32ac	20	10000	Supplemental
153009	32ac	20	10000	Supplemental
155050	125dc	3	-	Blade type automotive fuse
155060	32dc	3	-	-
155900	125ac	10	10000	Supplemental micro fuses
155900L	125ac	10	10000	Supplemental micro fuses
157900	125ac	10	-	Supplemental
1LFS101	600ac/dc	100	200000	Special Purpose
1LFS102	600ac/dc	400	200000	Special Purpose

254 followed by 00, 10, 12, 13 or 20, followed by 1 to 8 incl	600ac	10	10000	4.5 mm x 15 mm
281005	125ac	5	10000	Supplemental
281007	125ac	5	10000	Supplemental
281008	125ac	5	10000	Supplemental
281010	125ac	5	10000	Supplemental
286377	250ac	10	10000	4.5 mm x 15.5 mm
286677	250ac	10	10000	4.5 mm x 15.5 mm
342001 with or without one to three suffix letters and/or one prefix letter	250ac	20	10000	1/4 in. x 1-1/4 in
342004 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	15	10000	1/4 in. x 1-1/4 in
342006 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342012 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342014 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342021 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342022 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342024 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342028 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342038 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342048 with or without 1 to 3 incl., suffix letters and/or one prefix letter				

	250ac	20	10000	1/4 in. x 1-1/4 in
342058 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342828 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342838 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342848 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
342858 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
344006 with or without one to three suffix letters and/or one prefix letter	7ac	20	10000	1/4 in. x 1-1/4 in
344012 with or without one to three suffix letters and/or one prefix letter	16ac	20	10000	1/4 in. x 1-1/4 in
344024 with or without one to three suffix letters and/or one prefix letter	32ac	20	10000	1/4 in. x 1-1/4 in
344125 with or without one to three suffix letters and/or one prefix letter	125ac	20	10000	1/4 in. x 1-1/4 in
344250 with or without one to three suffix letters and/or one prefix letter	250ac	20	10000	1/4 in. x 1-1/4 in
344401 with or without one to three suffix letters and/or one prefix letter	7ac	20	10000	1/4 in. x 1-1/4 in
344402 with or without one to three suffix letters and/or one prefix letter	16ac	20	10000	1/4 in. x 1-1/4 in
344403 with or without one to three suffix letters and/or one prefix letter	32ac	20	10000	1/4 in. x 1-1/4 in

344405 with or without one to three suffix letters and/or one prefix letter	250ac	20	10000	1/4 in. x 1-1/4 in
345 followed by 1, followed by 0 or 2, followed by 1; 345 followed by 6, followed by 0, 1, 2, 3, followed by 1, 2, or 3; 345 followed by 7, followed by 0 or 1, followed by 1; 345 followed by 9, followed by 0, 1, 2 or 3, followed by 3; All with or without 1 to 3 suffix letters and/or one prefix letter				
	600ac/dc	20	10000	1/4 in. x 1-1/4 in or 5 mm x 20 mm
345 followed by 2, 3 or 5, followed by L, H, Q or R, followed by F or S, followed by 1 to 8 incl. All with or without one to three suffix letters and/or one prefix letter				
	300ac	20	10000	1/4 in. x 1-1/4 in.
346	250ac	15	10000	1/4 in. x 1-1/4 in.
352025 with or without 1 to 3 incl., suffix letters and/or one prefix letter				
	250ac	20	10000	1/4 in. x 1-1/4 in
354 followed by 0, 1, 6, 7, 8 or 9, followed by 01 to 12 incl., -21 or 41, with or without additional suffixes.				
	300ac	30	10000	1/4 in. x 1 -1/4 in
	600ac/dc	20	10000	1/4 in. x 1-1/4 in
482	125ac/dc	20	10000	Special Purpose Fuse
4822	125ac/dc	20	10000	Special Purpose Fuse
520001	250ac	10	-	5x20mm
520002	600ac/dc	10	100000	5 mm x 20 mm
520003	600ac	10	10000	5 mm x 20 mm
520004	600ac	10	10000	5 mm x 20 mm
520005	600ac/dc	10	10000	5 mm x 20 mm
520006	600ac/dc	10	10000	5 mm x 20 mm
520101	600ac	10	10000	5 mm x 20 mm
560 with or without suffix letters and/or one prefix letter	250ac	6.3	-	Supplemental micro fuses
562 with or without suffix letters and/or one prefix letter	250ac	6.3	-	Supplemental micro fuses
564 with or without suffix letters and/or one prefix letter	250ac	6.3	-	Supplemental micro fuses

570	250ac	6.3	10000	Supplemental micro fuses
571	250ac	6.3	10000	Supplemental micro fuses
571000	250ac	6.3	10000	Supplemental micro fuses
571004 With or without one to five suffix letters and/or one prefix letter	250ac	30	-	10x38mm
571007 With or without one to five suffix letters and/or one prefix letter	600ac	30	-	10x35mm
571008 With or without one to five suffix letters and/or one prefix letter	600ac	30	-	10x35mm
571027 With or without one to five suffix letters and/or one prefix letter	600ac	30	-	10x38mm
571028 With or without one to five suffix letters and/or one prefix letter	600ac	30	-	10x38mm
5710CC With or without one to five suffix letters and/or one prefix letter	600ac	30	200000	CC
571RCC With or without one to five suffix letters and/or one prefix letter	600ac	30	200000	CC
572007 With or without one to five suffix letters and/or one prefix letter	600ac	30	-	10x35mm
572008 With or without one to five suffix letters and/or one prefix letter	600ac	30	-	10x35mm
572027 With or without one to five suffix letters and/or one prefix letter	600ac	30	-	10x38mm
572028 With or without one to five suffix letters and/or one prefix letter	600ac	30	-	10x38mm

5720CC With or without one to five suffix letters and/or one prefix letter	600ac	30	200000	CC
572RCC With or without one to five suffix letters and/or one prefix letter	600ac	30	200000	CC
575	250ac	6.3	10000	Supplemental micro fuses
576	250ac	6.3	10000	Supplemental micro fuses
576000	250ac	6.3	10000	Supplemental micro fuses
64900001009	250ac/dc	20	-	-
64900001039	250ac/dc	20	-	-
64900003009	250ac/dc	20	-	-
64900003039	250ac/dc	20	-	-
868-062-000UL may be followed by additional suffixes.	125dc	15	-	Blade type automotive fuse
Cat. No. Series 245	300ac	10	10000	4.5 mm x 15 mm
D60030M Followed by 1 or 2, followed by S, P, C or Q, may be followed by Q and may be followed by R and may be followed by DIN, may be followed by R.				
	600ac	30	100000	10x38
D60030M3 Followed by S, P, C or Q, may be followed by Q and may be followed by R and may be followed by DIN, may be followed by R				
	600ac	30	100000	10x38
ILS101	600ac/dc	100	-	-
ILS101A	600dc	100	-	-
ILS102	600ac/dc	400	-	-
ILS103	600ac/dc	400	-	-
ILS104	600ac/dc	600	-	-
L60030CM3PQ	600ac	30	200000	CC and 10 mm x 38 mm
L60030M Followed by 1 or 2, followed by S, P, C or Q, may be followed by Q and may be followed by R and may be followed by DIN, may be followed by R.				

	600ac	30	100000	10x38
L60030M1SPQ	600ac/dc	30	-	-
L60030M2SPQ	600ac/dc	30	-	-
L60030M3 Followed by S, P, C or Q, may be followed by Q and may be followed by R and may be followed by DIN, may be followed by R				
	600ac	30	100000	10x38
L60030M3PCB	600ac	30	100000	10x38
L60030M3SPQ	600ac/dc	30	-	-
LEB Followed by A, B, C, D, J or YC, followed by A, B, C, D, J or YC, may be followed by -S				
	600ac	30	200000	10 X 38
LEX Followed by A, B, C, D, J or YC, followed by A, B, C, D, J or YC, may be followed by -S				
	600ac	30	200000	10 X 38
LEX-T Followed by A, B, C, D, J or YC, followed by A, B, C, D, J or YC, may be followed by -S				
	600ac	30	200000	10 X 38
LFFB0003Z	150ac/dc	800	2500	-
LFH250601SQ	250ac/dc	60	10000	-
LFH250602SQ	250ac/dc	60	10000	-
LFH250603SQ	250ac/dc	60	10000	-
LGR Followed by three digits, followed by Suffix "L". May be followed by three alphanumeric suffixes.				
	300ac	10	-	0.25in. X 1-.5 in.
LHR Followed by three digits, followed by Suffix "L". May be followed by three alphanumeric suffixes.				
	300ac	10	-	0.25in. X 1-.5 in.
LPHV followed by 000 f/b 1, 2, 3 or 4, f/b Z	600ac/dc	30	200000	10 x 38 mm
LPSM followed by 000, followed by 1, 2, 3 or 4, followed by Z CH, ZXID CH	600dc	30	200000	10 x 38 mm
LPSM followed by 000, followed by 1, 2, 3 or 4, followed by Z QC, ZXID QC	600ac/dc	30	200000	10 x 38 mm

LSCR001	700ac/dc	400	200000	Special Purpose
LSCR002	700ac/dc	800	200000	Special Purpose
LSCR101	1000ac/dc	400	200000	-
LSCR102	1000ac/dc	800	200000	-
LSCR103	1000ac/dc	1200	200000	-
MLMF Followed by three digits, followed by Suffix "L". May be followed by three alphanumeric suffixes.				
	300ac	10	-	0.25in. X 1-5 in.
Series 154 followed by three digits, indicating amp rating, may be followed by three letters and maybe followed by "L"				
	125ac	10	10000	Supplemental micro fuses
Series 157 followed by three digits, followed by three letters	125dc	10	-	Supplemental
Series 356 followed by 001, 002, 003, 004, 005, 006, 007, 008, 009, 010, 011 or 012.				
	600ac/dc	15	-	1/4 in. x 1-1/4 in
Series 359 followed by 001, 002, 003, 004, 005, 006, 007, 008, 009, 010, 011 or 012.				
	600ac/dc	15	-	1/4 in. x 1-1/4 in
SPFRHD4001ST	600ac/dc	400	10000	Class H or Special Purpose
SPFRHV4001ST	1000ac/dc	400	10000	Special Purpose

Marking: Company name or tradename "LF" and model designation.

Last Updated on 2020-04-29

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2020 UL LLC"