








- NOTES:
1. MATERIALS:
BASE/COVER: BLACK FR530
BOTTOM CAP: BLUE PA66
LATCH: YELLOW POM
 2. MAX. MAIN INPUT: 400A
 3. OPERATING TEMPERATURE RANGE: -40°C TO 85°C
 4. MB MOUNTING TORQUE: 10±2 Nm
 5. MAX. WIRE SIZE 105 sqmm OR AWG 4/0.



LTR	DATE	REVISION	CHK	APD
A	26/Jun/18	519497GCC-NEW RELEASE	FYUE	

4	873-716	COVER	1	EA
3	883-088	LATCH	2	EA
2	868-967	BASE	1	EA
1	883-094	BOTTOM CAP	2	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS () ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
COPIES TO	MATE SPEC			
1 9 18	SEE NOTE			
2 10 19	FINISH			
3 12 20	SEE NOTE			
4 13 21	DRW	FYUE	DATE	26/Jun/18
5 14 23	CHK		DATE	
6 15 33	APPD		DATE	
7 16 43			DATE	
8 17 53			DATE	
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-TH)				
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120
TOLERANCE	±0.1	±0.1	±0.2	±0.3
3RD ANGLE PROJECTION				
TITLE	UNSEALED 4-WAY ZCASE FUSE BOX			
METRIC ASSEMBLY	LITTELFUSE	REVISION	DRWG. NO.	OUTLINE
		A	0FHZ0003Z	

METRIC
ASSEMBLY

LITTELFUSE
DES PLAINES, ILLINOIS 60018

REVISION
A

DRWG. NO.
0FHZ0003Z

OUTLINE

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED