



Littelfuse®

Expertise Applied | Answers Delivered

Looking for a 2D Print?

Please visit the specific part number page to view the 2D print.

When viewing a series, please click on the specific part number you are looking for in the specifications table at the bottom of the page.

Specifications

Technical Resources

Related Products

Environmental Info

Access specifications, certifications, check availability and order parts below

Catalog #	Mounting Method	Fuse Type	Current Rating (Max)	Voltage Rating Max	Wire size	Ingress Protection	Temperature Maximum Celsius	Temperature Minimum Celsius	Compare
▲	▲	▲	▲	▲	▲	▲	▲	▲	
FHAS100	In-Line	ATO	20	32	12 AWG	IP67	85	-40	☐
FHAS100-BP	In-Line	ATO	20	32	12 AWG	IP67	85	-40	☐
FHAS101	In-Line	ATO	20	32	14 AWG	IP67	85	-40	☐
FHMS200	In-Line	MINI	20	32	12 AWG	IP67	85	-40	☐
FHMS200-BP				32	12 AWG	IP67	85	-40	☐
FHMS201				32	14 AWG	IP67	85	-40	☐

FHAS100

Once at the parts page, please scroll down to the bottom of the page and view the Technical Resources tab where you will find the part's 2D print and other part number related collateral.

Technical Resources

Environmental Info

View All

2D Prints

Spotlights

Datasheets

3D Model

Sealed In-Line ATO and MINI Fuse Holder FHAS100 2D Print

Part Number: FHAS100 and FHAS100-BP,

Sealed In-Line ATO & MINI Fuse Holders Spotlight

ATO-MINI-Sealed-Fuse-Holders Datasheet

ATO-MINI-Sealed-Fuse-Holders Datasheet

3D Model - Sealed In-Line ATO & MINI Fuse Holders 3D Model

3D Model - Sealed In-Line ATO & MINI Fuse Holders 3D Model

Sealed In Line ATO MINI Fuse Holder Datasheet

Sealed In Line ATO MINI Fuse Holder Datasheet

Sealed In-Line ATO and MINI Fuse Holder FHAS100 2D Print

Part Number: FHAS100 and FHAS100-BP