

ASQU / ASTU SERIES



Description

The ASQU and ASTU Series of 17.5 mm, knob adjustable, universal solid-state timers offer multiple functions, voltages, and time delay ranges. Choose one of 5 functions and 4 time delay ranges via 4 selection switches located on face of the unit. Adjustment through the time range is accomplished by an onboard knob.


The ASQU Series has quick connect terminals and the ASTU Series has terminal blocks.

Features & Benefits


FEATURES	BENEFITS
Universal AC or DC voltage	Choose from 24 to 240VAC or 9 to 110VDC models
Compact 17.5mm size	Allows for high rail density
Microcontroller based	Repeat Accuracy + / -1%
Multifunction: 5 timing functions	Reduce stocking requirements
Knob Adjustable Time Delay	Field adjustable delay ranging from 0.1s - 100m
0.7A steady, 10A inrush solid-state output	Provides 100 million operations in typical conditions.
Mounting fasteners included	Each unit ships with both surface and DIN rail quick mount adapters
Watchdog circuitry	Self monitoring and self correcting for improved performance

Wiring & Adjustment Diagrams

DELAY-ON-MAKE & RECYCLING



SINGLE SHOT, INTERVAL & DELAY-ON-BREAK



V = Voltage
L = Load
J = Wire Required for Interval Operation
S1 = Initiate Switch
UTL = Optional Untimed Load

ADJUSTMENTS

DOM	A ☐ B ☐
SS	A ☐ B ☐
R	A ☐ B ☐
DOB	A ☐ B ☐

DOM = Delay-on-Make
SS = Single Shot/Interval
R = Recycling
DOB = Delay-on-Break

R	M	S
0.1-10s	X1s	C ☐ E D ☐ F
1-100s	X10s	C ☐ E D ☐ F
10-1000s	X100s	C ☐ E D ☐ F
1-100m	X10m	C ☐ E D ☐ F

R = Range
M = Multiplier
S = Setting

Accessories



P1015-13 (AWG 10/12), **P1015-64** (AWG 14/16), **P1015-14** (AWG 18/22) **Female Quick Connect**
These 0.25 in. (6.35 mm) female terminals are constructed with an insulator barrel to provide strain relief.



P0500-178 Surface Mount Adapter
P0500-179 DIN Rail Mount Adapter
For use with the ASxx/DSxx Series timers.

Ordering Information

MODEL	INPUT VOLTAGE	CONNECTION
ASQUA3	24 to 240VAC	Quick Connects
ASQUD3	9 to 110VDC	Quick Connects
ASTUA3	24 to 240VAC	Terminal Blocks
ASTUD3	9 to 110VDC	Terminal Blocks

If you don't find the part you need, call us for a custom product 800-843-8848

ASQU / ASTU SERIES

Specifications

Time Delay

Type

Microcontroller based with ceramic resonator and watchdog circuitry

Adjustment

Knob with dial; 2 switches select 1 of 4 multipliers

Range*

0.1 - 10s, 1 - 100s, 10 - 1000s, 1 - 100m

Repeat Accuracy

±1% or ±50ms, whichever is greater

Tolerance

(Factory Calibration)

±2% or ±50ms, whichever is greater

Reset Time

≤ 300ms

Initiate Time

Single Shot & Delay-on-Break: ≤ 32ms

Time Delay vs Temp.

& Voltage

±2%, or ±50ms, whichever is greater

Input

Voltage

AC: 24 to 240VAC; -20% - 10%
DC: 9 to 110VDC; -0% - 20% @ -25°C
9.4 to 110VDC; -0% - 20% @ -40°C

AC Line Frequency/DC Ripple

50/60Hz / ≤ 10%

Output

Type

Solid state

Form

NO

Rating

0.7A steady state, 10A inrush

Voltage Drop

AC ≅ 2.5V @ 0.7A; DC ≅ 1.5V @ 0.7A

Protection

Surge

IEEE C62.41-1991 Level A

Circuitry

Encapsulated

Dielectric Breakdown

≥ 2000V RMS terminals to mounting surface

Polarity

DC units are reverse polarity protected

Mechanical

Mounting

Two base adaptors are available

DIN Rail

Snap on to 32 mm DIN 1 & 35 mm DIN 3 rail

Surface

Two #6 (M3.5 x 0.6) screws or quick mount fasteners

Dimensions

H 76.2 mm (3.0"); **W** 17.52 mm (0.69");
D 61.2 mm (2.41")

Termination

ASQU

0.25 in. (6.35 mm) male quick connect terminals

ASTU

0.197 in. (5 mm) push-on terminal blocks for up to #14 AWG (2.5 mm²) wire

Environmental

Operating/Storage

Temperature

-40° to 60°C / -40° to 85°C

Humidity


95% relative, non-condensing

Weight


≅ 4 oz (113 g)

Mounting Diagrams

P0500-178
SURFACE MOUNT
Inches (Millimeters)



P0500-179
DIN RAIL MOUNT
Inches (Millimeters)



*For CE approved applications, power must be removed from the unit when a switch position is changed.