

# ISF SERIES

## 250V SHOCK-SAFE AGC (3AG) PANEL-MOUNT GLASS FUSE HOLDER



03453LF2XP

### Specifications

<b>Current Rating Continuous:</b>	15A
<b>Current Max:</b>	20A
<b>Fuse Type:</b>	3AG Glass Fuses
<b>Mounting Method:</b>	Panel Mount
<b>Housing:</b>	PA66 GF30
<b>Recommended Torque:</b>	Mounting Torque: 15 Lbs.- In.
<b>Max Voltage Rating:</b>	250V

### Description

Compatible with AGC (3AG) glass fuses up to 20 amps, the ISF Series 250V Shock-Safe AGC (3AG) Panel-Mount Glass Fuse Holder features a low-profile body, finger-grip knob, and an anti-tease feature that eliminates circuit interruption when the knob is accidentally depressed.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/ISF](http://littelfuse.com/ISF)

### Applications

- Hole-Mounted Slow- or Fast-Blowing Automotive Fusing

### Features and Benefits

- Accepts AGC (3AG) glass fuses up to 20 amps (sold separately)
- Shock-Safe fuse holder design eliminates the possibility of electrical shock, as defined in IEC standards 65 and 257
- Anti-tease feature eliminates circuit interruption when the knob is accidentally depressed
- Straight 3/16" Quick Connect terminals for easy wiring
- Low-profile body is easy to install to a panel without a screwdriver
- UL listed and CSA certified

### Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	MAX CURRENT RATING	MAX VOLTAGE RATING
03453LF2XP	250V Shock-Safe AGC (3AG) Panel-Mount Glass Fuse Holder	3AG GLASS FUSES	PANEL MOUNT	20 AMPS	250 V