

UL Online Certifications Directory

[Home](#) [Quick Guide](#) [Contact Us](#) [UL.com](#)

JDYX.E10480 Fuses, Supplemental

Fuses, Supplemental

See General Information for Fuses, Supplemental

LITTELFUSE INC
SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

E10480

Type or Cat. No.	Size	Amps	V AC
Miscellaneous, cartridge enclosed, nonrenewable.			
Cat. Nos. 532, KLK*	13/32x1-1/2 in.	0.3-30	600
followed by .300 to 030 incl.			
Cat. Nos. 519, KLKD*	13/32x1-1/2 in.	0.3-30	600 dc
followed by .300 to 030 incl.			
Cat. Nos. F60C	13/32x1-1/2 in.	0.30 - 30	500ac/500dc
followed by .300 to 030 incl.			
Cat. No. KLQ	13/32x1-1/2 in.	1.0-6.0	600
followed by 001 to 006			

Cat. Nos. 533, FLM*	13/32x1-1/2 in.	0.1-30	250
followed by			
0.10 to 030 incl.			
Cat. Nos. 536, BLF*	13/32x1-1/2 in.	20.0-30.0	125
followed by 20.0 to			
30.0 incl.			
Cat. Nos. 537, BLS*	13/32x1 1-3/8 in.	0.2-5.0	600
followed by		6-10	250
.200 to 10 incl.			
Cat. Nos. 535, BLN,*	13/32 x 1-1/2 in.	0.5-30.0	250
followed by 0.5 to			
30.0 incl.;			
WP91770 (List 1-13)			
Cat. Nos. 536, BLF*	13/32 x 1-1/2 in.	.5-15	250
followed by			
.5 to 15 incl.			
Cat. No. EV60030	13/32x1-1/2 in.	30	600 ac/dc
Cat. No. FLA* followed	13/32 x 1 1/2 in.	0.1-30	125
by 0.10 to 030 incl.			
Cat. Nos. 538, FLQ*	13/32 x 1 1/2 in.	0.1-30	500
followed by			
.100 to 030 incl.			
Micro			
Cat. Nos. 874	3.6 x 10 mm.	0.100-10	250
Cat. Nos. 875	3.6 x 10 mm.	0.100-10	250
Cat. No. 875	3.6 x 10 mm.	12	125ac/32dc

Cat. No. 451	0.085 x 0.235 in.	0.062-5	125 ac/ dc
Cat. No. 453	0.085 x 0.235 in.	0.062-5	125 ac/ dc
Cat. No. 490	0.085 x 0.235 in.	0.062-5	125 ac/ dc
Cat. No. 450011MR	0.085 x 0.235 in.	0.062-5	125 ac/ dc
Miniature, cartridge enclosed, nonrenewable.			
Cat. No. 310278*	1/4 x 1 1/4 in.	3	250
Cat. No. 310279*	1/4 x 1 1/4 in.	7	125
Cat. No. 310296*	1/4 x 1-1/4 in.	15	250
Cat. No. 310299*	1/4 x 1-1/4 in.	10	250
Cat. No. 310306*	1/4 x 1-1/4 in.	7	125
Cat. Nos.*+ 312.010 to 312010 incl., 318.010 to 318010 incl.	1/4 x 1-1/4 in.	0.01-10.0	250
Cat. Nos. 313*+, 315*+ 313ID followed by *+ 0.01 to 008 incl.	1/4 x 1-1/4 in.	0.01-10.0	250
Cat. Nos.*+ 314.125 to 314015 incl., 324.125 to 324015 incl.	1/4 x 1-1/4 in.	0.125-15.0	250 125 dc
WP91768 (List 1-16, 101-116)			
Cat. Nos.*+ 326.250 to 326010 incl., WP91769 (List 101-134).	1/4 x 1-1/4 in.	0.25-10.0	250
Cat. Nos*+ 325.250 to 325010 incl., WP91769 (List 01-34)	1/4 x 1-1/4 in.	0.25-10.0 0.25-3	250 125 dc

Cat. No. LMF* followed by 0.3 to 10 incl.	1/4 x 1.82 with knob	0.3-10	300
Cat. No. LGR* followed by 0.5 to 15 incl.	1/4 x 1.82 with knob	0.5-15	300
Cat. Nos* . 300154, 309001, 30901.5	1/4 x 5/8 in.	1-1.5	125
Cat. Nos. 229*+ 230*+(with pigtails) followed by 0.25 to 03.5 incl.	4.5 x 15 mm	0.25-3.5	250
Cat. Nos. 229*+ 230*+(with pigtails) followed by 0.25 to 003 incl., WP90904 followed by List Nos. 01-10, 101-110	4.5 x 15 mm	0.25-3.0	310
Cat. No. 220010 +*	4.5 x 15 mm	.55	250
Cat. No. 220018, +*	4.5 x 15 mm	3	250
Cat. No. 220024, +*	4.5 x 15 mm	1	250
Cat. No. 220025, +*	4.5 x 15 mm	1.25	250
Cat. No. 220026, +*	4.5 x 15 mm	1.5	250
Cat. No. 220030, +*	4.5 x 15 mm	0.375	250
Cat. No. 220031, +*	4.5 x 15 mm	0.375	250
Cat. No. 220033, +*	4.5 x 15 mm	1.5	250
Cat. No. 220036, +*	4.5 x 15 mm	0.5	300
Cat. No. 220056*, +, 220057*+	4.5 x 15 mm	1.25	250 ac 125 dc
Cat. Nos. 224*+, 225*+, followed by .100	4.5 x 15 mm	0.1-3.5	250

to 3.5 incl.;			
WP90736 followed by			
(List 01-11, 101-111)			
Cat. No. 220043*+	4.5x15 mm	1.0	250
Cat. No. 220*+ followed by	4.5 x 15 mm	0.35	250
001, 002, 003, 004,			
006, 011 or 029; WP90400			
followed by List No.			
1, 4 or 6; WP90109			
followed by List No. 1			
Cat. Nos. 373*+, 375*+	1/4 x 1-1/4 in.	4.0-10.0	250
followed by 004		10.1-15.0	125
to 015 incl.			
Cat. Nos. 235*+, 236*+	5 mm x 20 mm	0.1-3.5	250
followed by .100		4.0-7.0	125
to 007 incl.			
Cat. No. 238*+, 239*+,	5 mm x 20 mm	0.08-3.5	250
followed by 0.08 to 3.5 incl.			
Cat. No. 238*+, 239*+	5 mm x 20 mm	4.0-7.0	125
followed by 004 to 007 incl.			
Cat. No. 237*+ followed by	5 mm x 20 mm	1-10	125
001 to 010 incl.			
Cat. No. 234*+	5 mm x 20 mm	1-10	250
followed by 001			
to 010 incl.			
Cat. No. 233*+	5 mm x 20 mm	1.0 to 10 incl.	125
followed by			
1.0 to 10 incl.			

61NM, 62NM+	1/4 X 1-1/4 in.	0.032-10.0	125 or 250
61S, 62S+	1/4 x 1-1/4 in.	0.032-5.0	125 or 250
65TS	1/4 x 1-1/4	1-15	250
485 Series**	3.96 x 11.43 mm	1 - 3.15	250 Vac/600 Vdc

Supplemental Fuse, Series 485 followed by suffix Nos. 001, 01.5, 002, 02.5, 3.15 with or without one prefix and with and without up to three additional suffix letters.

*With or without one prefix character and with or without additional suffix characters that signify options that do not affect the electrical characteristics.

+May be followed by P

**Optional prefix and/or suffix characters indicate options such as packaging, etc. and do not affect the electrical characteristics.

Last Updated on 2010-06-04

[Questions?](#)

[Print this page](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright ?2010 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2010 Underwriters Laboratories Inc.®"