



JDYX8.E67006 Fuses, Supplemental Certified for Canada - Component

Page Bottom

Fuses, Supplemental Certified for Canada - Component

[See General Information for Fuses, Supplemental Certified for Canada - Component](#)

LITTELFUSE WICKMANN WERKE

E67006

SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

Cartridge enclosed nonrenewable, Micro, Type 370 or 19370, rated 0.040-6.3A, 250 Vac; Type 372 or 19372, rated 0.040-6.3A, 250 Vac; Types 382, 383, rated 1-10A, 250/320 Vac.

Micro, Type 391, rated 125mA-4.0A, 65 Vac/dc.

Micro, Type TIP385, rated 350mA-1500mA, 125Vac.

Micro, Type 398, rated 125mA-4.0A, 65 Vac/dc.

Miniature, Cat. No. 193 or 19193, rated 0.32-6.3A, 250 Vac.

Cat. No. 375, rated 5-6.3A, 250Vac.

Cat. No. 354, rated 1-10 A, 440 V ac; Cat. No. 356 rated 1-10 A, 440 V ac; Cat. No. 358 rated 3.15-10 A, 500 V ac, 50 V dc.

Microfuses, Cat. No. 389 rated 0.06A, 250Vac.

Micro, Type 369, rated 0.8 -6.3A, 300 Vac; Type 392, rated 0.8-6.3A, 250Vac.

Cat. No. 400 rated 0.5-6.3A, 250VAC.

Cat. No. TE5 808 rated 1-2.5A, 250Vac, 450Vdc; 3.0-3.15A, 250Vac, 350Vdc; 4-5A, 250V ac/dc.

Type 399, rated 125 mA - 4.0 A.

Type 393, rated 3.0 A, 250 Vac.

Type TE7 807, rated 0.2-6.3 amp, 300 Vac.

Supplemental, Type 150+, rated 3.0A, 350 Vac.



Type 201, rated 0.032-1.25A, 250 Vac.

Type 462, rated 0.5-1.6A, 350 V ac, 350V dc, 2-4A, 250V ac, 250V dc, 350V ac, 350V dc.

+Pigtail leads.

++With or without Pigtail leads.



Marking: Company name and/or trademark  , catalog or type designation and Recognized Component Mark for Canada  .
Last Updated on 2011-03-23

[Questions?](#)

[Print this page](#)

[Notice of Disclaimer](#)

[Page Top](#)