



## JFHR2.E71611 Special-purpose Fuses - Component

[Page Bottom](#)

### Special-purpose Fuses - Component

[See General Information for Special-purpose Fuses - Component](#)

#### LITTELFUSE INC

E71611

SUITE 500  
8755 W HIGGINS RD  
CHICAGO, IL 60631 USA

**Cartridge fuses**, Cat. Nos. KLPC-200 through -600.

Cat. Nos. L25S001 through -800.

Cat. Nos. L50S001 through -030 .

Cat. Nos. L50S035 through -800.

Cat. Nos. L70S001 through -800.

Cat. Nos. L17T70 through -800A, -1200A .

Cat. Nos. LDC150 through -600.

Cat. Nos. KLC-0 through -800.

Cat. Nos. JLLS-900, -1000, -1100, -1200.

Cat. Nos. TLS1 through -125, rated 1-125A, 170 Vdc.

Cat. Nos. TLS-1 through -100L, TLS V1 through -100, TLS1 through -100LB, TLS1 through -100LS, rated 1-100A, 170 Vdc, TLS-1MB through -100MB, rated 1-100A, 170 Vdc.

Cat. No. TLN1-600, rated 1-600A, 170V dc.

Type MIDI, Part. No. 498 040 through 100.

Series 297 followed by 002 through 030, rated 2-30A, 32 Vdc / 125 Vac.

Series 298 followed by 080 through 200, rated 80-200A, 32 Vdc.

Series 299 followed by 020, 030, 040, 050, 060, 070 or 080, rated 20-80A, 32 Vdc.

Series 446, 447 followed by 002, 003, 004, 005, 07.5 or 010, may be followed by "P", rated 2, 3, 4, 5, 7.5, 10A, 350 Vac; Series 446, 447 followed by 003, may be followed by "P", rated 3A, 140 Vac.

Series 495, Jcase, followed by 020, 030, 040, 050 or 060, rated 20, 30, 40, 50, 60A, 58 Vdc.

Cat. No. 496, followed by 100, 150 or 200 rated 100, 150 and 200A, 32V dc.

Cat. No. 257APC rated 1-40A, 32 Vdc; Cat. No. 257003 rated 3A, 32 Vdc, 32 Vac.

Cat. No. 257-3A, 25 Vac/32 Vdc.

Cat. No. JLLS 0-30V, JLLS 0-30LS rated 1-30A, 600 Vac.



LA70QS8022F, LA70QS8022FI.

**Special purpose cartridge fuses**, Cat. Nos. JLLN, followed -L, -LS, or -V followed by 35 through 60.

**Special purpose fuses**, Cat. Nos. CNN-10, CNN-35, CNN-40, CNN-50, CNN-60, CNN-80, CNN-90, CNN-100, CNN-125, CNN-150, CNN-175, CNN-200, CNN-225, CNN-250, CN-275, CNN-300, CNN-325, CNN-350, CNN-400, CNN-500, CNN-600, CNN-700, CNN-800, CNL-35, CNL-40, CNL-50, CNL-60, CNL-80, CNL-100, CNL-125, CNL-130, CNL-150, CNL-175, CNL-200, CNL-225, CNL-250, CNL-275, CNL-300, CNL-325, CNL-350, CNL-400, CNL-500.

Cat. Nos. CNN-35 E, CNN-40 E, CNN-50 E, CNN-60 E, CNN-80 E, CNN- 90 E, CNN- 100 E, CNN-125 E, CNN-150 E, CNN-175 E, CNN- 200 E, CNN- 225-E, CNN- 250 E, CNN-275 E, CNN-300 E, CNN-325 E, CNN- 350 E, CNN-400 E, CNN-500 E, CNN-700 E, CNN-800 E.

Cat. Nos. CNL-35E, CNL-40E, CNL-50E, CNL-60E, CNL-80E, CNL-100E, CNL-125E, CNL-130E, CNL-150E, CNL-175E, CNL-200E, CNL-225E, CNL-250E, CNL-275E.

Cat. No. 581, rated 10-800A, 48VDC.

Cat. Nos. KLKD.750.HXL and KLKD005.HXL, rated 3/4A and 5A, 600V AC/DC.

Series 997, rated 2-30 A, 58 Vdc.

**Special purpose semi-conductor protection fuses**, Cat. Nos. LA50QS101, LA50QS151, LA50QS201, LA50QS251, LA50QS301.

Cat. Nos. SPF001, SPF002, SPF003, SPF004, SPF005, SPF006, SPF008, SPF010, SPF012, SPF015, SPF020, SPF025, SPF030, SPF001-R, SPF002-R, SPF003-R, SPF004-R, SPF005-R, SPF006-R, SPF008-R, SPF010-R, SPF012-R, SPF015-R, SPF020-R, SPF025-R, SPF030-R.

Cat. Nos. SPFR250, SPFR300, SPFR350, SPFR400.

**Special cartridge fuse, nonrenewable**, Cat. No. LGD followed by 1, 3, 6, 8, 10, 12, 15, 20, 25, 30.

Marking: Company name or "LF" and type, series or catalog designation.

Last Updated on 2011-04-29

[Questions?](#)

[Print this page](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright © 2011 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2011 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

