



## IZLT.E14721 Fuseholders, Cartridge Fuse

Page Bottom

### Fuseholders, Cartridge Fuse

See General Information for Fuseholders, Cartridge Fuse

**LITTELFUSE INC**

SUITE 500  
8755 W HIGGINS RD  
CHICAGO, IL 60631 USA

E14721

Cat. No. L60030 or D60030 followed by C or G, followed by 1, 2 or 3, followed by C, P, Q or S, may be followed by Q and/or R, may be followed by DIN, may be followed by R.

Cat. Nos. L60060C-1C, L60060C-2C, L60060C-3C, L60060C-AC.

Cat. No. LFC60060, followed by 1, 2, or 3, followed by C, may be followed by ID.

Series L30030G, D30030G followed by 1, 2 or 3, followed by S, P, C or Q, may be followed by Q and/or R, may be followed by DIN, may be followed by R; Cat. No. LFG48030 followed by 1, 2, or 3, followed by PQDINR or SQDINR.

Cat. Nos. LH25030, -25060, -25100, -25200, -25400, -25600, -60030, -60060, -60100, -60200, -60400, -60600 followed by 1, 2 or 3, followed by C, P or S, may be followed by R or may be followed by suffix - CU.

Cat. Nos. LJ60030, -60060, -60100, -60200 followed by 1, 2 or 3, followed by C or S, may be followed by R.

Cat. No. LJ60030 followed by 1P, 2P, 3P, AC, AP, AS, may be followed by R.

Cat. Nos. LR25030, -25060, -25100, -25200, -25400, -25600, -60030, -60060, -60100, -60200, -60400, -60600 followed by 1, 2 or 3, followed by C, P or S, may be followed by R, may be followed by suffix - CU.

Cat. Nos. LT30030, -30060, -30100, -30200, -30400, -30600, -60030, -60060, -60100, -60200, -60400, -60600 followed by 1, 2 or 3, followed by C, S, may be followed by R.

Cat. Nos. LPSJ30-1, -30-2, -30-3, -30-1ID, 30-2ID, -30-3ID, -60-1, -60-2, -60-3, -60-1ID, -60-2ID, -60-3ID.

Cat. No. LG300 followed by 1, 2 or 3, followed by 01, 02, 03, 51, 52 or 53, followed by C, PQ or SQ.

Cat. No. LT601002CMB.

Cat. Nos. LINK001C, LINK002C, LINK003C.

Cat. Nos. LT60200-1CS, LT60200-3CS, LT60600-1CS, LT60600-3CS, LFT301001CS, LFT301003CS, LFT302001CS, LFT302003CS, LFT306001CS, LFT306003CS, LFT601001CS, LFT601003CS, LFT602001CS, LFT602003CS, LFT606001CS, and LFT606003CS.

Cat. No. LFJ60030 followed by -1 or -3, followed by SR, PR or CR; Cat. No. LFJ60060 followed by -1 or -3, followed by CR; Cat. No. LFJ60100 followed by -1 or -3, followed by CR.

Cat. No. LFR25030 followed by 1, 2 or 3, followed by C, P or S; Cat. No. LFH25030 followed by 1, 2 or 3, followed by C, P or S; Cat. No. LFR60030 followed by 1, 2 or 3, followed by C, S or P, may be followed by ID; Cat. No. LFH60030 followed by 1, 2 or 3, followed by C, S or P, may be followed by ID.

Cat. No. LFR25060 followed by 1, 2 or 3, followed by C, may be followed by ID; Cat. No. LFH25060 followed by 1, 2 or 3, followed by C, may be followed by ID; Cat. No. LFR60060 followed by 1, 2 or 3, followed by C, may be followed by ID; Cat. No. LFH60060 followed by 1, 2 or 3, followed by C, may be followed by ID.

Cat. No. LFR25100 followed by 1 or 3, followed by C, may be followed by ID; Cat. No. LFH25100 followed by 1 or 3, followed by C, may be followed by ID; Cat. No. LFR60100 followed by 1 or 3, followed by C, may be followed by ID; Cat. No. LFH60100 followed by 1 or 3, followed by C, may be followed by ID.

Cat. No. LFR60030 followed by 1, 2 or 3, followed by C, S or P, may be followed by ID; Cat. No. LFH60030 followed by 1, 2 or 3, followed by C, S or P, may be followed by ID.

Cat. No. LPSC followed by 000, followed by 1, 2, 3 or 4, followed by Z CH.

Cat. No. LPSC followed by 000, followed by 1, 2, 3 or 4, followed by ZXID CH.

Cat. No. LEC or LEY followed by A, B, C, D, J or YC, may be followed by -S

Cat. No. LFT30030 followed by 1, 2 or 3, followed by C; Cat. No. LFT30060 followed by 1, 2 or 3, followed by C; Cat. No. LFT60030 followed by 1, 2 or 3, followed by C, S or P; Cat. No. LFT60060 followed by 1, 2 or 3, followed by C.

Cat. Nos. LFPSJ301.Z, LFPSJ302.Z, LFPSJ303.Z, LFPSJ301.ZXID, LFPSJ302.ZXID, LFPSJ303.ZXID.

Class J, Cat. Nos. LFPSJ601.Z, LFPSJ602.Z, LFPSJ603.Z, LFPSJ601.ZXID, LFPSJ602.ZXID, LFPSJ603.ZXID.

Cat. No. LFR60200 followed by 1 or 3, followed by C; Cat. No. LFR25200 followed by 1 or 3, followed by C; Cat. No. LFR60600 followed by 1 or 3, followed by C; Cat. No. LFR60400 followed by 1 or 3, followed by C; Cat. No. LFR25600 followed by 1 or 3, followed by C; Cat. No. LFR25400 followed by 1 or 3, followed by C; Cat. No. LFH60200 followed by 1 or 3, followed by C; Cat. No. LFH25200 followed by 1 or 3, followed by C; Cat. No. LFH60600 followed by 1 or 3, followed by C; Cat. No. LFH60400 followed by 1 or 3, followed by C; Cat. No. LFH25600 followed by 1 or 3, followed by C; Cat. No. LFH25400 followed by 1 or 3, followed by C.

Cat. No. LFJ60600 followed by 1 or 3, followed by C; Cat. No. LFJ60400, followed by 1 or 3, followed by C; Cat. No. LFJ60200 followed by 1 or 3, followed by C.

Cat. No. LFT60400 followed by 1 or 3, followed by CS; Cat. No. LFT30400, followed by 1 or 3, followed by CS.

Cat. No.	Voltage Rating	Current Rating	Interrupting Rating RMS Symmetrical	Fuse Class
LFJ60030	600 ac	30	200,000	J
	600 dc	30	20,000	J
LFJ60060	600 ac	60	200,000	J
	600 dc	60	20,000	J
LFJ60100	600 ac	100	200,000	J
	600 dc	100	20,000	J
LFR25030 followed by 1, 2 or 3, followed by C, P or S	250 ac	30	200,000	R
	250 dc	30	20,000	R
LFH25030 followed by 1, 2 or 3, followed by C, P or S	250 ac	30	10,000	H
	250 dc	30	10,000	H
LFR60030 followed by 1, 2 or 3, followed by C, P or S, may be followed by ID	600 ac	30	200,000	R
	600 dc	30	20,000	R
LFH60030 followed by 1, 2 or 3, followed by C, P or S, may be followed by ID	600 ac	30	10,000	H
	600 dc	30	10,000	H
LFR25060 followed by 1, 2 or 3, followed by C, may be followed by ID	250 ac	60	200,000	R
	250 dc	60	20,000	R
LFH25060 followed by 1, 2 or 3, followed by C, may be followed by ID	250 ac	60	10,000	H
	250 dc	60	10,000	H
LFR60060 followed by 1, 2 or 3, followed by C, may be followed by ID	600 ac	60	200,000	R
	600 dc	60	20,000	R
LFH60060 followed by 1, 2 or 3, followed by C, may be followed by ID	600 ac	60	10,000	H

	600 dc	60	10,000	H
LFH60060	600 ac	60	10,000	H
LFR60060	600 ac	60	200,000	R
LFR25100 followed by 1 or 3, followed by C, may be followed by ID	250 ac	100	200,000	R
	250 dc	100	20,000	R
LFH25100 followed by 1 or 3, followed by C, may be followed by ID	250 ac	100	10,000	H
	250 dc	100	10,000	H
LFR60100 followed by 1 or 3, followed by C, may be followed by ID	600 ac	100	200,000	R
	600 dc	100	20,000	R
LFH60100 followed by 1 or 3, followed by C, may be followed by ID	600 ac	100	10,000	H
	600 dc	100	10,000	H
LFJ60030 followed by 1, 2 or 3, followed by C, P or S, may be followed by ID	600 ac	30	200,000	J
	600 dc	30	20,000	J
LFJ60060 followed by 1, 2 or 3, followed by C, may be followed by ID	600 ac	60	200,000	J
	600 dc	60	20,000	J
LFJ60100 followed by 1 or 3, followed by C, may be followed by ID	600 ac	100	200,000	J
	600 dc	100	20,000	J
LPSC followed by 000, followed by 1, 2, 3 or 4, followed by Z CH	600 ac	30	200,000	CC
	600 dc	30	20,000	CC
LPSC followed by 000, followed by 1, 2, 3 or 4, followed by ZXID CH	600 ac	30	20,000	CC
	600 dc	30	20,000	CC
LEC or LEY followed by A, B, C, D, J or YC, may be followed by -S	600 ac	30	200,000	CC
L60060C-1C	600	60	200,000	CD
L60060C-2C	600	60	200,000	CD
L60060C-3C	600	60	200,000	CD
L60060C-AC	600	60	200,000	CD
LFC60060 followed by 1, 2, or 3, followed by C, may be followed by ID	600 ac	60	200,000	CD
	600 dc	60	20,000 dc	CD
LFPSJ301.Z	600	30	200,000	J
LFPSJ302.Z	600	30	200,000	J
LFPSJ303.Z	600	30	200,000	J
LFPSJ301.ZXID	600	30	200,000	J
LFPSJ302.ZXID	600	30	200,000	J
LFPSJ303.ZXID	600	30	200,000	J
LFPSJ601.Z	600	60	200,000	J
LFPSJ602.Z	600	60	200,000	J
LFPSJ603.Z	600	60	200,000	J
LFPSJ601.ZXID	600	60	200,000	J
LFPSJ602.ZXID	600	60	200,000	J
LFPSJ603.ZXID	600	60	200,000	J
LFR60200 followed by 1 or 3, followed by C.	600 ac	200	200,000	R

LFR25200 followed by 1 or 3, followed by C.	250 ac	200	200,000	R
LFR60600 followed by 1 or 3, followed by C	600 ac	600	200,000	R
LFR60400 followed by 1 or 3, followed by C	600 ac	400	200,000	R
LFR25600 followed by 1 or 3, followed by C	250 ac	600	200,000	R
LFR25400 followed by 1 or 3, followed by C	250 ac	400	200,000	R
LFH60200 followed by 1 or 3, followed by C.	600 ac	200	10,000	H
LFH25200 followed by 1 or 3, followed by C.	250 ac	200	10,000	H
LFH60600 followed by 1 or 3, followed by C	600 ac	600	10,000	H
LFH60400 followed by 1 or 3, followed by C	600 ac	400	10,000	H
LFH25600 followed by 1 or 3, followed by C	250 ac	600	10,000	H
LFH25400 followed by 1 or 3, followed by C	250 ac	400	10,000	H
LFJ60600 followed by 1 or 3, followed by C.	600 ac	600	200,000	J
LFJ60400 followed by 1 or 3, followed by C.	600 ac	400	200,000	J
LFJ60200 followed by 1 or 3, followed by C.	600 ac	200	200,000	J
LFT60400 followed by 1 or 3, followed by CS.	600 ac	400	200,000	T
LFT30400 followed by 1 or 3, followed by CS.	300 ac	400	200,000	T
LT60200 followed by -1 or -3, followed by CS	600 ac	200	200,000	T
LT60600 followed by -1 or -3, followed by CS	600 ac	600	200,000	T
LFT30100 followed by 1 or 3, followed by CS	300 ac	100	200,000	T
LFT30200 followed by 1 or 3, followed by CS	300 ac	200	200,000	T
LFT30600 followed by 1 or 3, followed by CS	300 ac	600	200,000	T
LFT60100 followed by 1 or 3, followed by CS	600 ac	100	200,000	T
LFT60200 followed by 1 or 3, followed by CS	600 ac	200	200,000	T
LFT60600 followed by 1 or 3, followed by CS	600 ac	600	200,000	T

Last Updated on 2011-03-22

[Questions?](#)

[Print this page](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright © 2011 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2011 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

