



JDYX2.E67006 Fuses, Supplemental - Component

[Page Bottom](#)

Fuses, Supplemental - Component

[See General Information for Fuses, Supplemental - Component](#)

LITTELFUSE WICKMANN WERKE

E67006

800 E NORTHWEST HWY
DES PLAINES, IL 60016 USA

Cartridge enclosed nonrenewables, Micro, Cat. No. 419, rated 6A-10A, 125 Vac/dc, 11-15 A, 65 V ac/dc.

Micro, Cat. No. 275+ or 19275+, rated 10A, 125Vdc.

Micro, Type 457, rated 500mA-2.0A, 250 Vac.

Micro, Type 370 or 19370, rated 0.040-6.3A, 250 Vac; Type 372 or 19372, rated 0.040-6.3A, 250 Vac; Types 382, 383, rated 1-6.3A, 320 Vac, 8-10 A, 50 A, 320 Vac, 100 A, 250 Vac; Type 383, rated 1-4A, 100A, 300Vac.

Micro, Type 391, rated 125mA-4.0A, 65 Vac/dc.

Micro, Type 392, rated 0.8 -6.3A, 250 Vac.

Micro, Type TIP385, rated 350mA-1500mA, 125Vac.

Micro, Type 399, rated 125mA-4.0A, 65 Vac/dc.

Miniature, Cat. No. 195 or 19195, rated 0.032-12.5A, 250 Vac; or Cat. No. 19196, rated 32mA-6.3A, 250 Vac.

Micro, Type 398, rated 125mA-4.0A, 65 Vac/dc.

Microfuses, Cat. Nos. FCD12 Series may be followed by additional letters and /or numbers, rated 0.2-2.5A, 64 Vdc/32 Vac. rated 0.2 amps - 2.5 amps, 64 Vdc/32 Vac.

Cat. Nos. FCD12 Series may be followed by additional letters and /or numbers, rated 3.0 -5.0A, 32 Vdc.

Cat. Nos. FCD08 Series may be followed by additional letters and /or numbers, rated 0.2-2.5 A, 50 V DC/25 Vac. FCB08 Series may be followed by additional letters and /or numbers, rated 0.2-2.5 A, 50 V DC/25 Vac.

Cat. Nos. FCD08 Series may be followed by additional letters and /or numbers, rated 1.0-4.0A, 32 Vdc, 4.1-5.0A, 24 Vdc. FCB08 Series may be followed by additional letters and /or numbers, rated 1.0-4.0A, 32 Vdc, 4.1-5.0A, 24 Vdc.

Cat. Nos. FCD06 Series may be followed by additional letters and /or numbers, rated 0.2A-2.0A, 36 Vdc, 2.05-2.5, 32Vdc, 2.6A-5.0A, 24Vdc. FCB06 Series may be followed by additional letters and /or numbers, rated 0.2A-2.0A, 36 Vdc, 2.05-2.5, 32Vdc, 2.6A-5.0A, 24Vdc .

Cat. Nos. FCD04 Series may be followed by additional letters and /or numbers, rated 0.2A -2.0A @ 30 Vdc. FCB04 Series may be followed by additional letters and /or numbers, rated 0.2A -2.0A @ 30 Vdc.

Cat. Nos. FCD04 Series may be followed by additional letters and /or numbers, rated 1.0-3.15A, 24 Vdc. FCB04 Series may be followed by additional letters and /or numbers, rated 1.0-3.15A, 24 Vdc.

Cat. No. FCS06 Series may be followed by additional letters and/or numbers, rated 0.5-5.0A, 32 Vdc.

Cat. No. 389 rated 0.06A, 250Vac.

Miniatures, Cat. No. 181 or 19181, rated 0.125 -10A, 250 Vac.

Cat. No. 193 or 19193, rated 0.32-6.3A, 250 Vac.

Cat. No.194++ or 19194++, rated 0.315-6.3A , 250 Vac; Cat. No. 194 or 19194, rated 8-16A, 250 Vac.

Cat. No.354 or 19354, rated 1-10A , 440 Vac; Cat. No. 356 or 19356, rated 1-10A, 440 V ac.

Cat. No. 19358 or 358, rated 3.15-10A 500 Vac and 50 Vdc.

Cat. No. 375, rated 5-6.3A, 250Vac.

Supplementals, Type 150+, rated 3.0A, 350 Vac.

Type 199, rated 0.8-6.3A, 250 vac.

Type 201, rated 0.032-1.25A, 250 Vac.

Type 462, rated 0.5-1.6A, 350 Vac, 350 Vdc; rated 0.5-3.15A, 350 Vac, 350 Vdc.

Type 462, rated 4A, 350 Vac, 350 Vdc.

Surface mount micro fuse, Type 420, rated 500 mA - 5A, 80 Vdc.

+Pigtail leads.

++With or without Pigtail leads.



Marking: Company name or trademarks , , and amp rating.

Last Updated on 2008-06-17

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2008 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

