



JDYX2.E67006 Fuses, Supplemental - Component

[Page Bottom](#)

Fuses, Supplemental - Component

[See General Information for Fuses, Supplemental - Component](#)**LITTELFUSE WICKMANN WERKE**

E67006

SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

Cartridge enclosed nonrenewable, Micro, Type 370 or 19370, rated 0.040-6.3A, 250 Vac; Type 372 or 19372, rated 0.040-6.3A, 250 Vac; Types 382, 383, rated 1-10A, 250/320 Vac.

Micro, Type 391, rated 125mA-4.0A, 65 Vac/dc.

Micro, Type TIP385, rated 350mA-1500mA, 125Vac.

Micro, Type 398, rated 125mA-4.0A, 65 Vac/dc.

Microfuses, Micro, Type 369, rated 0.8 -6.3A, 300 Vac; Type 392, rated 0.8-6.3A, 250Vac.

Cat. No. 389 rated 0.06A, 250Vac.

Cat. No. 400 rated 0.5-6.3A, 250VAC.

Cat. No. TE5 808 rated 1-2.5A, 250Vac, 450Vdc; 3.0 -3.15A, 250Vac, 350Vdc; 4-5A, 250V ac/dc.

Type 399, rated 125 mA - 4.0 A.

Type 393, rated 3.0 A, 250 Vac.

Type TE7 807, rated 0.2-6.3 amp, 300 Vac.

Miniature, Cat. No. 193 or 19193, rated 0.32-6.3A, 250 Vac.

Cat. No. 375, rated 5-6.3A, 250Vac.

Cat. No. 354, rated 1-10 A, 440 V ac; Cat. No. 356 rated 1-10 A, 440 V ac; Cat. No. 358 rated 3.15-10 A, 500 V ac, 50 V dc.

Supplemental, Type 150+, rated 3.0A, 350 Vac.

Type 201, rated 0.032-1.25A, 250 Vac.

Type 462, rated 0.5-1.6A, 350 V ac, 350V dc, 2-4A, 250V ac, 250V dc, 350V ac, 350V dc.

+Pigtail leads.

++With or without Pigtail leads.



Marking: Company name or trademarks , , , catalog or type and amp rating.

Last Updated on 2011-03-23

[Questions?](#)[Print this page](#)[Notice of Disclaimer](#)[Page Top](#)

Copyright © 2011 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2011 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

