





REVISIONS					
REV.	DESCRIPTION	DATE	GCF / ECR	DESIGNED	APPROVED
A	Initial release	09-Jun-22		L.Dal Molin	M.Tinto




SCALE 1:2

CHARACTERISTICS AND PRESCRIPTIONS


- Rated voltage: 12V-24V
- Voltage limit operation: 16V ÷ 32V
- Maximum continuous current in the main contact: 350A at 23 °C
- Maximum current of short duration in the main contact: 2500A for 5sec at 23 °C
- Number of electrical operations: 5000
- Number of mechanical operations: 5000
- Fix the M6 screws: 8 ±1 Nm
- Fix the M12 nut: 20 ±2 Nm
- Handle operation torque: 3.5 ±2 Nm
- Accessories: 08099500 - 08099800 - 00902500




Electrical diagram



Fixing holes



DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.								
linear dimensions								
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000		
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3		
angle (for range of lengths)								
up to 10	>10 50	>50 120	>120 400					
±1°30'	±1°	±0°30'	±0°15'					
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL							
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL							
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE							
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS							
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE							
NAME		DATE		 Littelfuse® Expertise Applied Answers Delivered				
DRAWN		L. Dal Molin					09-Jun-22	
CHECKED		-					-	
		-					-	
FORM NO: CVP-PE40-0013 REV A				TITLE				
FIRST ANGLE PROJECTION				BATT SWITCH REMOVED HANDLE				
				GASKET M12				
				SIZE: A3	DWG. NO. OL-08098980	OUTLINE REV. A		
DO NOT SCALE DRAWING				SCALE 1:2		SHEET 1 OF 1		