


2

1



Mechanical Dimensions :

A	B	C	D	E
0.076" $\pm$ 0.008" (1.9304 $\pm$ 0.2032mm)	0.049" $\pm$ 0.008" (1.2446 to 0.2032 mm)	0.055" Max (1.397 Max)	0.008" Min (2X) (0.2032mm Min (2X))	Solder Plated Terminations Ends

Electrical Specifications :

Resistance (25 °C) Ω	Resistance Tolerance, $\pm\%$	Temp, Coefficient (%/ °C)	Beta(K)	Temp Rating(°C)	Power Rating(V)	Packaging
100 to 100000	1 to 10	3.31 to 4.4	2000~5000	-55~ +150	300~400	Tape & Reel

A	Initial Release	RKM	04/04/2023	
Rev	Description	By	Date	ECO NO
Revision History				
Reference Legacy No.		USPxxxx REV x		

Project Code	XXXXXX		 Littelfuse®		
	Third Angle Projection				
Units	Inch(mm)		Division	IBU - Temperature Sensors	
General Tolerances 0.X = ± 0.X 0.XX = ± 0.XX 0.XXX = ± 0.XXX			Title	End Banded NTC Thermistor Chips-0805	
			Finished Product Part Number	NSKR	
Drawn By	RKM		Internal No.	NSKR	
				Rev	A
Date	04/04/2023		Size	A	
				Do Not Scale	
				Sheet	1 of 1

B

A

2

1