



CHARACTERISTICS AND PRESCRIPTIONS

- Rated voltage $9 \div 16V$
- Max direct current 300A
- Max short time current 2000A for 5 sec at 23°C

SAP drawing number:
Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.					
linear dimensions					
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000
±0,2	±0,3	±0,5	±0,8	±1,2	±3
angle (for range of lengths)					
up to 10	>10 50	>50 120	>120 400		
±1°30'	±1°	±0°30'	±0°15'		
	FIT / FUNCTION CRITICAL CHARACTERISTICS SYMBOL				
<S>	SAFETY / COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL				
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE				
(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS IDENTIFICATION PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS				
CP	DENOTES CP DIMENSIONS - MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE				
NAME		DATE			
DRAWN L. Dal Molin		29/04/2019			
CHECKED	-	-			
	-	-			
	-	-			
FORM NO.: CVP-PE40-0013 REV A		TITLE			
FIRST ANGLE PROJECTION		ELECTRICAL MAIN BATTERY SWITCH			
		SIZE (+) A2		DWG. NO. 	OUTLINE REV. A
DO NOT SCALE DRAWING		SCALE 1:1			SHEET 1 OF 1