

NOTES: (UNLESS OTHERWISE SPECIFIED)

1. ASSOCIATED CAD FILE DEFINES ALL NONDIMENSIONED FEATURES

2. PRODUCT WEIGHT: 0.18 Kg

3. MAXIMUM TERMINAL STUD TORQUE: 13.56 NM (120IN-LB)

4. FRONT PANEL MOUNT IN 67MM (2-5/8") HOLE

5. TERMINAL HARDWARE: 3/8"-16 NUT SERRATED FLANGE, STAINLESS STEEL

6. REAR PANEL MOUNT IN 60MM [2-3/8"] HOLE






7. REAR PANEL MOUNT HEX FEATURE FOR #10 NUTS



8. ELECTRICAL SPECIFICATOIN:  
- MAX OPERATING VOLTAGE: 32V DC  
- MAX CONTINUOUS CURRENT: 300A  
- CRANKING RATING (30 SEC) (1X4/0 CABLE): 1,250A

9. INGRESS RATING: IP67 & IP69K

10. IGNITION PROTECTION: MEETS ISO 8846 7 SAE J1171

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	Per EC# 515700: INITIAL RELEASE	3/22/2016	J. LIU
	B	PER EC#515935: ADDED A PERPENDICULARITY CALLOUT	5/26/2016	J. LIU



DIMENSIONS ARE IN MM.		DRAWN		NAME		DATE			
DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI / ASME Y14.5M-1994		CHECKED		J. LIU		11/15/2013		Expertise Applied   Answers Delivered	
THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.								805 W. ORCHARD DR., STE. 6, BELLINGHAM, WA 98225	
								Phone (360)738-9010 Fax (360)738-0372	
								Switch Master Panel Mt	
		THIRD ANGLE PROJECTION				SIZE		DWG. NO.	
						C		OL-880062	
						SCALE 1:1		REV. B	
								SHEET 1 OF 1	