



| REVISION |          |                                  |
|----------|----------|----------------------------------|
| REV      | DATE     | DESCRIPTION                      |
| A        | 12/20/18 | 520065GCP - RELEASE MRY          |
| B        | 11/14/19 | 521621ECP/D - ADD TOLERANCES MRY |
| C        | 3/1/22   | 524893ECP/D - ADD NOTES MRY      |

|     |  |
|-----|--|
| <S> | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE   |
| ●   | DENOTES CRITICAL CHARACTERISTICS.  |
| CPK | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE   |
| ST  | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |
| CP  | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.               |

**A**

|           |                 |           |                            |
|-----------|-----------------|-----------|----------------------------|
| MATL SPEC |                 | FINISH    |                            |
| DRW myork | DATE 10/16/2018 | SCALE NTS | FINISH GOOD WT GRAMS/PIECE |

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

|                      |  |
|----------------------|--|
| 3RD ANGLE PROJECTION |  |
|----------------------|--|

**TITLE** TLS-LR OUTLINE



|          |              |              |
|----------|--------------|--------------|
| REVISION | DRWG NO.     | SHEET 1 OF 1 |
| C        | OL-0TLS000LR |              |

NOTES:

RECOMMENDED HARDWARE: #8 SLOTTED HEX WASHER HEAD MACHINE SCREW

TORQUE: 10 IN-LB