




NOTES:

- CONTACT RATING: 125 AMPS CONTINUOUS, 750 INTERMITTENT (15 SECONDS "ON", 5 MINUTES OFF) 12 TO 36 VDC (CARRY ONLY)
- SILVER CONTACT SURFACES
- A POLE AND B POLE ARE SEPERATE INSULATED POLES
- OPERATING TEMPERATURE RANGE: -40° C THROUGH +85° C
- O-RING SEAL @ MOUNTING STEM
- GASKET SEAL @ TERMINAL INSULATOR
- HENCOL SEAL @ CASE, MOUNTING STEM & LOCATING PIN
- MOUNTING TORQUE: 20 FT. LBS. (27 Nm)
- STUD TORQUE: 4.42-7.37 FT. LBS. (6-10 Nm)
- ALL STEEL PARTS ARE PLATED
- ALL DIMENSIONS ARE FOR REFERENCE ONLY
- COMPATABLE WITH COLE HERSEE LOCKOUT KITS 24505 & -01, FACE PLATE P/N 82065-02 & CABLE TERMINALS P/N 3188
- LEVER TORQUE FROM OFF TO ON 17-25 IN-LBS.(23-34 Nm) TORQUE FROM ON TO OFF 15-20 IN-LBS (20-27 Nm)
- RATING: CIRCUIT A-A 400 AMPS @ 24Vdc 30 SECONDS ON 2 MINUTES OFF CIRCUIT B-B 100 AMPS CONTINUOUS

Revision Control Record				Rev.	Description of Change	ECN No.	Date	Note: unless noted otherwise all dimension are <u>AFTER</u> plating Tolerances: Unless otherwise specifically noted, the following are default tolerances:			PROPRIETARY INFORMATION		Special Characteristics:		 Phn: 617-268-2100 Web: www.colehersee.com	Description:	Drawing / Part No.:	Current Rev.
Rev.	Description of Change	ECN No.	Date					2-places ± 0.02 [0.5]	3-places ± 0.005 [0.13]	Angular ± 1°	All information contained herein, is proprietary to Littelfuse. Unauthorized use or reproduction is prohibited.	3RD ANGLE PROJECTION	CC Critical Characteristic, relating to Safety and/or Regulatory Compliance	X Significant Characteristic relating to Process Control				
A	RELEASED DRAWING	12285	8/23/12					Unless otherwise specified dimensions are in inches. Dimensions in brackets [] are in millimeters.										
								"REF" = Non-Toleranced Reference Dimension, shown for clarification purposes only.										
								Note: All tolerances are Non-Cumulative.										
								FORM CHT-6 (1/12)	Used On or Ref: EX28843, 75912		Scale: 1:1	Drawn BY: DPS	Date Drawn: 1/17/11	Pg. 1 of 1				