






REVISIONS					
REV.	DESCRIPTION	DATE	GCF / ECR	DESIGNED	APPROVED
A	Initial release	21-Jun-22		L.Dal Molin	M.Tinto




SCALE 1:2


CHARACTERISTICS AND PRESCRIPTIONS

- Rated voltage: 12V-24V
- Voltage limit operation: 16V ÷ 32V
- Maximum continuos in the main contact 350A at 23°C
- Maximum current of short duration in the main contact: 2500A for 5 sec ar23°C
- Numbers of electrical and mechanical cycles: 5.000
- Fix the M6 screws: 8 ± 1 Nm
- Fix the M10/M12 nuts: 20 ± 2 Nm
- Accessories: 08095500



Electrical diagram



DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10		>10 50	>50 120	>120 400		
±1°30'		±1°	±0°30'		±0°15'	
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
NAME		DATE		 Littelfuse® Expertise Applied Answers Delivered		
DRAWN		L. Dal Molin 15-Jun-22				
CHECKED		- -				
-		- -				
-		-		TITLE		
FORM NO: CVP-PE40-0013 REV A						
FIRST ANGLE PROJECTION						
				MANUAL CHANGEOVER SWITCH		
				DGC/350		
				SIZE: A3 DWG. NO. OL-08099400 OUTLINE REV. A		
DO NOT SCALE DRAWING				SCALE 1:2		SHEET 1 OF 1