






	4	3	2	1	
REVISIONS					
REV.	DESCRIPTION	DATE	GCF / ECR	DESIGNED	APPROVED
A	Initial release	22-Jun-22		L.Dal Molin	M.Tinto






- CHARACTERISTICS AND PRESCRIPTION**
- Nominal voltage: 12-24V
 - Maximum direct current: 150A
 - Maximum short time current: 1200A for 5 sec at 23°C
 - Number of electrical and mechanical cycles: 5.000
 - M10 nuts tightening torque: 20 ± 2 Nm
 - Fix the device to th structure by screws and nuts M6 with tightening torque 3.3 ± 0.2 Nm

Electrical diagram



Fixing holes



DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.																
linear dimensions																
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000										
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3										
angle (for range of lengths)																
up to 10	>10 50	>50 120	>120 400													
±1°30'	±1°	±0°30'	±0°15'													
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL															
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL															
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE															
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS															
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE															
<table><tr><th>NAME</th><th>DATE</th></tr><tr><td>L. Dal Molin</td><td>22-Jun-22</td></tr><tr><td>CHECKED -</td><td>-</td></tr><tr><td>-</td><td>-</td></tr><tr><td>-</td><td>-</td></tr></table>			NAME	DATE	L. Dal Molin	22-Jun-22	CHECKED -	-	-	-	-	-	<div> Littelfuse®</div> <div>Expertise Applied Answers Delivered</div>			
NAME	DATE															
L. Dal Molin	22-Jun-22															
CHECKED -	-															
-	-															
-	-															
FORM NO: CVP-PE40-0013 REV A			TITLE													
FIRST ANGLE PROJECTION			MANUAL BDS IGC/175-C													
			SIZE: A2	DWG. NO. OL-08080380	OUTLINE REV. A											
DO NOT SCALE DRAWING			SCALE 1:1		SHEET 1 OF 1											