



PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR
OFHM0001ZXJ	94±5 [3.70±0.2]	94±5 [3.70±0.2]	13±2 [.51±0.08]	13±2 [.51±0.08]	BLACK	BLACK
OFHM0001ZXJ-RW	94±5 [3.70±0.2]	94±5 [3.70±0.2]	13±2 [.51±0.08]	13±2 [.51±0.08]	RED	RED
OFHM0001ZXJA	95±5 [3.74±0.2]	3850±30 [151.57±1.2]	NO END STRIP	NO END STRIP	RED	RED
OFHM0001ZXJB	460±5 [18.11±0.2]	120±5 [4.72±0.2]	13±2 [.51±0.08]	13±2 [.51±0.08]	BLACK	BLACK

LTR	DATE	REVISION	CHK	APD
A	03/29/07	63207 - RELEASE BRK		
B	06/06/07	85498D - CHG TOL FROM ±1 TO ±1.5, CHG NOTE 6 BRK		
C	07/24/07	85549D - CHG TO CHARTED DRAWING, HOUSING HEIGHT TO 18.0 AND STRIP TOLERANCE TO ±2, BRK		
D	08/04/09	000738ER-ADDED OFHM0001ZXJ-RW CHG, BLACK WIRE TO "SEE CHART" IN NOTE 3 GMB		
E	08/09/12	505766ECA-ADDED DIMENSION 7.5 ±0.25 FYUE		
F	01/14/14	509993ERA-RELEASE OFHM0001ZXJB FYUE		
G	04/30/15	511837ECA-REMOVE MODEL NAME OF HOLDER MATERIAL FYUE		



IN-LINE FUSEHOLDER SHOWN
WITH MINI FUSE INSTALLED
(NOT INCLUDED)

- NOTES:
1. HOLDER MATERIAL: BLACK TPV
 2. CONTACTS: COPPER ALLOY: TIN-PLATED
 3. WIRE: SEE CHART, 14 AWG STRANDED COPPER, 125°C RATED, GXL WIRE
 4. CRIMP: MUST MEET SAE/USCAR 21 STANDARD
 5. RATING: MAX. 20A, 32Vdc
 6. FUSEHOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION
 7. MAX TEMPERATURE 125°C

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES								
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.								
	DENOTES CRITICAL CHARACTERISTICS.							
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE							
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS							
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE							
COPIES TO		MATL SPEC						
		SEE NOTES						
1	9	18	FINISH					
2	10	19						
3	12	20						
		SEE NOTES						
4	13	21	DRW	BRK	DATE	03/29/07	SCALE	1:1
5	14	23	CHK		DATE		SUPER DR	
6	15	33	APPD		DATE		FINISH GOOD WT	
7	16	43						GRAMS/PIECE
8	17	53						
TOLERANCE UNLESS OTHERWISE SPECIFIED								
ONE PLACE DEC +/- .3			THREE PLACE DEC +/- .100					
TWO PLACE DEC +/- .15			ANGULAR +/- 1°					
3RD ANGLE PROJECTION		TITLE						
		MINI IN-LINE FUSEHOLDER						
		REVISION		DRWG. NO.		OUTLINE		
DES PLAINES, ILLINOIS 60016		G		OFHM0001ZXJ				

METRIC

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED