



MOUNTING SPECS:

STUD SIZE: M12 x 1.75 - 6H ∇ 13.0 [0.51]





STUD TORQUE (REFERENCE ONLY): 45-55 Nm

| REVISION | | |
|----------|----------|--|
| REV | DATE | DESCRIPTION |
| A | 3/13/20 | 522085GCP - RELEASE MRY |
| B | 3/23/20 | 522118ECP/D - UPDATE LENGTH MRY |
| C | 10/25/23 | 526838ECP/D - ADD VIEW W/O MICROSWITCH MRY |

FUSE WITH MICROSWITCH





FUSE



FUSE WITH MICROSWITCH

FOR REFERENCE ONLY

| | | | |
|---|--|--|--|
| <S> | | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE | |
| ● | | DENOTES CRITICAL CHARACTERISTICS. | |
| CPK | | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE | |
| ST | | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. | |
| CP | | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE. | |
| MATL SPEC | | FINISH | |
| DRW myork | | DATE 3/9/2020 | SCALE NTS |
| | | FINISH GOOD WT GRAMS/PIECE | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994 | | | |
| 3RD ANGLE PROJECTION | | | |
|  | | | |
| TITLE | | | |
| PSX SIZE 3XL FLUSH MOUNT (FL) FUSE OUTLINE | | | |
|  Littelfuse® CHICAGO, ILLINOIS 60631 | | REVISION C | DRWG NO. SHEET 1 OF 1 OL-PSX3XLFL0000 |