






LTR	DATE	REVISION	CHK	APD
A	01/22/14	510030ERA-RELEASE FYUE		
B	07/18/14	510793ECA-ADD DIMENSTONS FYUE		



-				
-				
-				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
COPIES TO		MATL SPEC		
		Mapex PA66 A0520FN-03 (30%GF)		
1 9 18	FINISH			
2 10 19	NONE			
3 12 20				
4 13 21	DRW	FYUE	DATE	SCALE
5 14 23			01/22/14	1:1
6 15 33	CHK		DATE	SUPER DR
7 16 43				
8 17 53	APPD		DATE	FINSH GOOD WT
GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)				
DIMENSION	0.5 - 3	UP TO 3 OVER 3 - 6	UP TO 6 OVER 6 - 30	UP TO 30 OVER 30 - 120
TOLERANCE	+0.1	+0.1	+0.2	+0.3
UP TO 400 OVER 400				
3RD ANGLE PROJECTION		TITLE		
		BASE		
		REVISION	DRWG. NO.	OUTLINE
		B	OL-868-163	
CHICAGO, USA 773-628-1000				

METRIC
COMPONENT

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)