

$\varnothing 30.94 \pm 0.381$
[$\varnothing 1.218 \pm 0.015$]

4.75 ± 0.15
[0.187 ± 0.006]

22.73 ± 0.89
[0.895 ± 0.035]

10.41
[0.410]

19.18
[0.755]

129.16 ± 1.59
[5.085 ± 0.063]

106.30 ± 1.59
[4.185 ± 0.063]

73.03
[2.875]

88.77 ± 1.59
[3.495 ± 0.063]

REVISION

REV	DATE	DESCRIPTION
A	7/18/23	526718GCP - RELEASE MRY

1				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL

<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE
●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC		FINISH	
DRW JMoler	DATE 6/23/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994



TITLE

L70QS 125-200A OUTLINE



REVISION	DRWG NO.	SHEET 1 OF 1
A	OL-L70QS200	