

30410

$$\begin{array}{r} 1235 \\ 1265 \end{array} \quad \begin{array}{r} 3136 \\ 3213 \end{array}$$

TYR.

44 [11 17]

$$\begin{array}{r} 365 \\ \underline{385} \end{array} \quad \begin{array}{r} 9 \overline{) 27} \\ 9 \underline{) 77} \end{array}$$

Technical drawing of a mechanical part with dimensions and tolerances:

- Top horizontal dimension: $50 \begin{bmatrix} 12 \\ 70 \end{bmatrix}$
- Left vertical dimension: $425 \begin{bmatrix} 10 \\ 79 \end{bmatrix}$ and $455 \begin{bmatrix} 11 \\ 53 \end{bmatrix}$
- Right vertical dimension: $25 \begin{bmatrix} 6 \\ 35 \end{bmatrix} \text{ DIA}$
- Bottom horizontal dimension: $30 \begin{bmatrix} 7 \\ 62 \end{bmatrix}$

PAR: NO	AMP RATING
---------	---------------

DO NOT SCALE



Cole Hersee Co.

CIRCUIT BREAKER	30410
-----------------	-------