



REV.		DESCRIPTION	REVISIONS		
A		FIRST ISSUE OF OUTLINE DRAWING	DATE	DESIGNED	APPROVED
			02-July-2020	Gasparini	Tinto



MECHANICAL CHARACTERISTICS




- Numbers of electrical and mechanical operations: 100.000
- Tightening torque nuts M10/M12: 20 ± 2 Nm
- Tightening torque nuts M5/M6: 1.6 ± 0.4 Nm

ELECTRICAL CHARACTERISTICS

- Nominal voltage range: 12 + 24 V
- Maximum continuous current on main contacts: 250A
- Maximum short time current on main contacts: 2000A at 23°C for 30sec

PRESCRIPTIONS



- (*): Marking of date of manufacturing according to standard LITTELFUSE
- (\$): To apply the label indifferently on one box side or the opposite
- (£): Cap for M5 pos. coil pin identification, to remove during TGC installation on vehicle
- It is prudent to fixing the product to the structure using M8 screws and flat washers under the head



Vista da A

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.					
linear dimensions					
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000
±0,2	±0,3	±0,5	±0,8	±1,2	±2
angle (for range of lengths)					
up to 10	>10 50	>50 120	>120 400	>400 1000	>1000 2000
±1°30'	±1°	±0°30'	±0°15'	±0°15'	±0°15'
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL				
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL				
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE				
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS				
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE				
NAME		DATE			
DRAWN	L. Dal Molin	20/05/2019			
CHECKED	-	-			
	-	-			
	-	-			
FORM NO. CVP-PE40-0013 REV A		TITLE			
FIRST ANGLE PROJECTION		REMOTE CONTROL SWITCH TGC			
		12V(Positive or negative disc connection) OL-08094900			
DO NOT SCALE DRAWING		SCALE 1:1		SHEET 1 OF 1	