

USP8528 Thermistor Probe




Description

Littelfuse offers Stainless probe assemblies suitable for a wide range of temperature sensing applications. If the dimensions and electrical characteristics on this product won't work for your requirements, please contact us for further assistance.

Features

- High Accuracy
- Stainless Steel Spring Strain Relief
- PFA Insulated Lead Wire
- 125°C Max Operating Temperature


Dimensions



Dimensions in inches.

A	B	C
0.250" ± 0.090" Strip	1.00" ± 0.250"	0.188" ± 0.005"
D	E	F
2.250" ± 0.060"	12.0" ± 1.00"	0.125" Nom OD

Part Numbering System



Note: Not all combinations of Part Number codes are available. Contact Littelfuse for details.

Specifications

Part Number	Resistance Ohms @25°C	R-T Curve	Beta (K) 0-50°C	Temperature Rating (°C)
USP8528	10000	J	3892	-55 to +125

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics